

EFM8 Laser Bee Family EFM8LB1 Data Sheet



The EFM8LB1, part of the Laser Bee family of MCUs, is a performance line of 8-bit microcontrollers with a comprehensive analog and digital feature set in small packages.


These devices offer state-of-the-art performance by integrating 14-bit ADC, internal calibrated temperature sensor (\pm 3 °C), and up to four 12-bit DACs into small packages, making them ideal for the most stringent analog requirement applications. With an efficient, pipelined 8051 core with maximum operating frequency at 72 MHz, various communication interfaces, and four channels of configurable logic, the EFM8LB1 family is optimal for many embedded applications.

EFM8LB1 applications include the following:

- · Optical network modules
- Precision instrumentation
- Industrial control and automation
- Smart sensors

KEY FEATURES

- Pipelined 8-bit 8051 MCU Core with 72 MHz operating frequency
- Up to 29 multifunction I/O pins
- One 14-bit, 900 ksps ADC
- Up to four 12-bit DACs with synchronization and PWM capabilities
- Two low-current analog comparators with built-in reference DACs
- Internal calibrated temperature sensor (±3 °C)
- Internal 72 MHz and 24.5 MHz oscillators accurate to ±2%
- Four channels of Configurable Logic
- 6-channel PWM / PCA
- · Six 16-bit general-purpose timers



1. Feature List

The EFM8LB1 device family are fully integrated, mixed-signal system-on-a-chip MCUs. Highlighted features are listed below.

- Core:
 - Pipelined CIP-51 Core
 - Fully compatible with standard 8051 instruction set
 - 70% of instructions execute in 1-2 clock cycles
 - 72 MHz maximum operating frequency
- Memory:
 - Up to 64 kB flash memory (63 kB user-accessible), in-system re-programmable from firmware in 512-byte sectors
 - Up to 4352 bytes RAM (including 256 bytes standard 8051 RAM and 4096 bytes on-chip XRAM)
- · Power:
 - Internal LDO regulator for CPU core voltage
 - · Power-on reset circuit and brownout detectors
- I/O: Up to 29 total multifunction I/O pins:
 - Up to 25 pins 5 V tolerant under bias
 - Selectable state retention through reset events
 - · Flexible peripheral crossbar for peripheral routing
 - 5 mA source, 12.5 mA sink allows direct drive of LEDs
- · Clock Sources:
 - Internal 72 MHz oscillator with accuracy of ±2%
 - Internal 24.5 MHz oscillator with ±2% accuracy
 - Internal 80 kHz low-frequency oscillator
 - External CMOS clock option (up to 50 MHz)
 - External RC oscillator (up to 3.2 MHz)

- Analog:
 - 14/12/10-Bit Analog-to-Digital Converter (ADC)
 - Internal calibrated temperature sensor (±3 °C)
 - 4 x 12-Bit Digital-to-Analog Converters (DAC)
 - 2 x Low-current analog comparators with adjustable reference
- Communications and Digital Peripherals:
 - 2 x UART, up to 3 Mbaud
 - SPI[™] Master / Slave, up to 12 Mbps
 - SMBus™/I2C™ Master / Slave, up to 400 kbps
 - I²C High-Speed Slave, up to 3.4 Mbps
 - 16-bit CRC unit, supporting automatic CRC of flash at 256byte boundaries
 - 4 Configurable Logic Units
- Timers/Counters and PWM:
 - 6-channel Programmable Counter Array (PCA) supporting PWM, capture/compare, and frequency output modes
 - 6 x 16-bit general-purpose timers
 - Independent watchdog timer, clocked from the low frequency oscillator
- On-Chip, Non-Intrusive Debugging
 - · Full memory and register inspection
 - Four hardware breakpoints, single-stepping
- Pre-programmed UART or SMBus bootloader

With on-chip power-on reset, voltage supply monitor, watchdog timer, and clock oscillator, the EFM8LB1 devices are truly standalone system-on-a-chip solutions. The flash memory is reprogrammable in-circuit, providing nonvolatile data storage and allowing field upgrades of the firmware. The on-chip debugging interface (C2) allows non-intrusive (uses no on-chip resources), full speed, in-circuit debugging using the production MCU installed in the final application. This debug logic supports inspection and modification of memory and registers, setting breakpoints, single stepping, and run and halt commands. All analog and digital peripherals are fully functional while debugging. Device operation is specified from 2.2 V up to a 3.6 V supply. Devices are available in 4x4 mm 32-pin QFN, 3x3 mm 24-pin QFN, 32-pin QFP, or 24-pin QSOP packages. All package options are lead-free and RoHS compliant.

2. Ordering Information




Figure 2.1. EFM8LB1 Part Numbering

All EFM8LB1 family members have the following features:

- · CIP-51 Core running up to 72 MHz
- Three Internal Oscillators (72 MHz, 24.5 MHz and 80 kHz)
- SMBus
- I2C Slave
- SPI
- 2 UARTs
- · 6-Channel Programmable Counter Array (PWM, Clock Generation, Capture/Compare)
- Six 16-bit Timers
- Four Configurable Logic Units
- 14-bit Analog-to-Digital Converter with integrated multiplexer, voltage reference, temperature sensor, channel sequencer, and directto-XRAM data transfer
- Two Analog Comparators
- 16-bit CRC Unit
- Temperature range: -40 to +105 °C

In addition to these features, each part number in the EFM8LB1 family has a set of features that vary across the product line. The product selection guide shows the features available on each family member.

Table 2.1. Product Selection Guide

Ordering Part Number	Flash Memory (kB)	RAM (Bytes)	Digital Port I/Os (Total)	ADC0 Channels	Voltage DACs	Comparator 0 Inputs	Comparator 1 Inputs	Bootloader Type	Bootloader Pins	Pb-free (RoHS Compliant)	Package
EFM8LB12F64E-C-QFN32	64	4352	29	20	4	10	9	UART	P0.4 / P0.5 ³	Yes	QFN32
EFM8LB12F64E-C-QFP32	64	4352	28	20	4	10	9	UART	P0.4 / P0.5 ³	Yes	QFP32

it)

Ordering Part Number	Flash Memory (kB)	RAM (Bytes)	Digital Port I/Os (Total)	ADC0 Channels	Voltage DACs	Comparator 0 Inputs	Comparator 1 Inputs	Bootloader Type	Bootloader Pins	Pb-free (RoHS Compliant	Package
EFM8LB12F64E-C-QFN24	64	4352	20	12	4	6	6	UART	P0.4 / P0.5 ³	Yes	QFN24
EFM8LB12F64E-C-QSOP24 ¹	64	4352	21	13	4	6	7	UART	P0.4 / P0.5 ³	Yes	QSOP24
EFM8LB12F64ES0-C-QFN32	64	4352	29	20	4	10	9	SMBus	P0.2 / P0.3 ³	Yes	QFN32
EFM8LB12F64ES0-C-QFN24	64	4352	20	12	4	6	6	SMBus	P0.2 / P0.3 ³	Yes	QFN24
EFM8LB12F64ES1-C-QFN32	64	4352	29	20	4	10	9	SMBus	P0.2 / P0.4 ³	Yes	QFN32
EFM8LB12F64ES1-C-QFN24	64	4352	20	12	4	6	6	SMBus	P0.2 / P0.4 ³	Yes	QFN24
EFM8LB12F32E-C-QFN32	32	2304	29	20	4	10	9	UART	P0.4 / P0.5 ³	Yes	QFN32
EFM8LB12F32E-C-QFP32	32	2304	28	20	4	10	9	UART	P0.4 / P0.5 ³	Yes	QFP32
EFM8LB12F32E-C-QFN24	32	2304	20	12	4	6	6	UART	P0.4 / P0.5 ³	Yes	QFN24
EFM8LB12F32E-C-QSOP24 ¹	32	2304	21	13	4	6	7	UART	P0.4 / P0.5 ³	Yes	QSOP24
EFM8LB12F32ES0-C-QFN32	32	2304	29	20	4	10	9	SMBus	P0.2 / P0.3 ³	Yes	QFN32
EFM8LB12F32ES0-C-QFN24	32	2304	20	12	4	6	6	SMBus	P0.2 / P0.3 ³	Yes	QFN24
EFM8LB12F32ES1-C-QFN32	32	2304	29	20	4	10	9	SMBus	P0.2 / P0.4 ³	Yes	QFN32
EFM8LB12F32ES1-C-QFN24	32	2304	20	12	4	6	6	SMBus	P0.2 / P0.4 ³	Yes	QFN24
EFM8LB11F32E-C-QFN32	32	2304	29	20	2 ²	10	9	UART	P0.4 / P0.5 ³	Yes	QFN32
EFM8LB11F32E-C-QFP32	32	2304	28	20	2 ²	10	9	UART	P0.4 / P0.5 ³	Yes	QFP32
EFM8LB11F32E-C-QFN24	32	2304	20	12	2 ²	6	6	UART	P0.4 / P0.5 ³	Yes	QFN24
EFM8LB11F32E-C-QSOP24 ¹	32	2304	21	13	2 ²	6	7	UART	P0.4 / P0.5 ³	Yes	QSOP24
EFM8LB11F32ES0-C-QFN32	32	2304	29	20	2 ²	10	9	SMBus	P0.2 / P0.3 ³	Yes	QFN32
EFM8LB11F32ES0-C-QFN24	32	2304	20	12	2 ²	6	6	SMBus	P0.2 / P0.3 ³	Yes	QFN24
EFM8LB11F32ES1-C-QFN32	32	2304	29	20	2 ²	10	9	SMBus	P0.2 / P0.4 ³	Yes	QFN32
EFM8LB11F32ES1-C-QFN24	32	2304	20	12	2 ²	6	6	SMBus	P0.2 / P0.4 ³	Yes	QFN24
EFM8LB11F16E-C-QFN32	16	1280	29	20	2 ²	10	9	UART	P0.4 / P0.5 ³	Yes	QFN32
EFM8LB11F16E-C-QFP32	16	1280	28	20	2 ²	10	9	UART	P0.4 / P0.5 ³	Yes	QFP32
EFM8LB11F16E-C-QFN24	16	1280	20	12	2 ²	6	6	UART	P0.4 / P0.5 ³	Yes	QFN24
EFM8LB11F16E-C-QSOP24 ¹	16	1280	21	13	2 ²	6	7	UART	P0.4 / P0.5 ³	Yes	QSOP24
EFM8LB11F16ES0-C-QFN32	16	1280	29	20	2 ²	10	9	SMBus	P0.2 / P0.3 ³	Yes	QFN32
EFM8LB11F16ES0-C-QFN24	16	1280	20	12	2 ²	6	6	SMBus	P0.2 / P0.3 ³	Yes	QFN24
EFM8LB11F16ES1-C-QFN32	16	1280	29	20	2 ²	10	9	SMBus	P0.2 / P0.4 ³	Yes	QFN32

Ordering Part Number	Flash Memory (kB)	RAM (Bytes)	Digital Port I/Os (Total)	ADC0 Channels	Voltage DACs	Comparator 0 Inputs	Comparator 1 Inputs	Bootloader Type	Bootloader Pins	Pb-free (RoHS Compliant)	Package
EFM8LB11F16ES1-C-QFN24	16	1280	20	12	2 ²	6	6	SMBus	P0.2 / P0.4 ³	Yes	QFN24
EFM8LB10F16E-C-QFN32	16	1280	29	20	0	10	9	UART	P0.4 / P0.5 ³	Yes	QFN32
EFM8LB10F16E-C-QFP32	16	1280	28	20	0	10	9	UART	P0.4 / P0.5 ³	Yes	QFP32
EFM8LB10F16E-C-QFN24	16	1280	20	12	0	6	6	UART	P0.4 / P0.5 ³	Yes	QFN24
EFM8LB10F16E-C-QSOP24 ¹	16	1280	21	13	0	6	7	UART	P0.4 / P0.5 ³	Yes	QSOP24
EFM8LB10F16ES0-C-QFN32	16	1280	29	20	0	10	9	SMBus	P0.2 / P0.3 ³	Yes	QFN32
EFM8LB10F16ES0-C-QFN24	16	1280	20	12	0	6	6	SMBus	P0.2 / P0.3 ³	Yes	QFN24
EFM8LB10F16ES1-C-QFN32	16	1280	29	20	0	10	9	SMBus	P0.2 / P0.4 ³	Yes	QFN32
EFM8LB10F16ES1-C-QFN24	16	1280	20	12	0	6	6	SMBus	P0.2 / P0.4 ³	Yes	QFN24

Note:

1. End of life.

2. DAC0 and DAC1 are enabled on devices with 2 DACs available.

3. See 3.10 Bootloader for more information on the bootloader types and pin usage.

Table of Contents

2. Ordering Information	1.	Feature List	2
3.1 Introduction 5 3.2 Power 5 3.3 I/O 5 3.4 Clocking 10 3.5 Counters/Timers and PWM 10 3.6 Communications and Other Digital Peripherals 11 3.7 Analog 14 3.8 Reset Sources 16 3.9 Debugging 16 3.10 Bootloader 16 4.1 Electrical Specifications 16 4.1.1 Recommended Operating Conditions 16 4.1.2 Power Consumption 16 4.1.3 Reset and Supply Monitor 21 4.1.4 Flash Memory 22 4.1.5 Power Management Timing 22 4.1.6 Internal Oscillators 22 4.1.7 External Oscillator 22 4.1.8 External Oscillator 22 4.1.1 Temperature Sensor 22 4.1.1 Temperature Sensor 22 4.1.1 Temperature Sensor 22 4.1.14 Congurators	2.	Ordering Information	3
3.2 Power	3.	System Overview	8
3.3 I/O		3.1 Introduction	8
3.3 I/O		3.2 Power	9
3.4 Clocking			
3.5 Counters/Timers and PWM. 10 3.6 Communications and Other Digital Peripherals 11 3.7 Analog. 14 3.8 Reset Sources 14 3.8 Reset Sources 16 3.9 Debugging 16 3.10 Bootloader 16 4. Electrical Specifications 16 4.1 Electrical Characteristics 16 4.1.1 Recommended Operating Conditions 16 4.1.2 Power Consumption 17 4.1.3 Reset and Supply Monitor 21 4.1.4 Flash Memory 21 4.1.5 Power Management Timing 22 4.1.6 Internal Oscillators 22 4.1.7 External Clock Input 22 4.1.8 External Oscillator 22 4.1.10 Voltage Reference 22 4.1.11 Temperature Sensor 22 4.1.12 1.8 V Internal LDO Voltage Regulator 22 4.1.14 Comparators 33 4.1.15 Configurable Logic 33 4.1.16 Port I/O 33 4.1.18 SPI 36			
3.6 Communications and Other Digital Peripherals 11 3.7 Analog. 14 3.8 Reset Sources 14 3.9 Debugging 14 3.10 Bootloader 16 4. Electrical Specifications 16 4.1 Electrical Characteristics 16 4.1.1 Recommended Operating Conditions 16 4.1.2 Power Consumption 16 4.1.3 Reset and Supply Monitor 21 4.1.4 Flash Memory 22 4.1.5 Power Management Timing 22 4.1.6 Internal Oscillators 22 4.1.7 External Clock Input 22 4.1.8 External Oscillator 22 4.1.10 Voltage Reference 227 4.1.11 Temperature Sensor 22 4.1.12 Northeral LDO Voltage Regulator 22 4.1.13 DACs 22 4.1.14 Comparators 33 4.1.15 Configurable Logic 33 4.1.16 Port I/O 33 4.1.18 SPI 35		-	
3.7 Analog. .14 3.8 Reset Sources .16 3.9 Debugging .16 3.10 Bootloader .16 4. Electrical Specifications .16 4.1 Electrical Characteristics .18 4.1.1 Recommended Operating Conditions .16 4.1.2 Power Consumption .16 4.1.3 Reset and Supply Monitor .12 4.1.4 Flash Memory .11 4.1.5 Power Management Timing .22 4.1.6 Internal Oscillators .22 4.1.7 External Clock Input .22 4.1.8 External Oscillator .22 4.1.9 ADC .22 4.1.10 Voltage Reference .227 4.1.11 Temperature Sensor .226 4.1.12 I.8 V Internal LDO Voltage Regulator .22 4.1.14 Comparators .22 4.1.15 Configurable Logic .33 4.1.16 Port I/O .33 4.1.18 SPI .35			
3.8 Reset Sources .15 3.9 Debugging .16 3.10 Bootloader .16 4. Electrical Specifications .16 4.1 Electrical Characteristics .18 4.1.1 Recommended Operating Conditions .16 4.1.2 Power Consumption .16 4.1.3 Reset and Supply Monitor .19 4.1.4 Flash Memory .21 4.1.5 Power Management Timing .22 4.1.6 Internal Oscillators .22 4.1.7 External Clock Input .22 4.1.8 External Oscillator .22 4.1.9 ADC .22 4.1.10 Voltage Reference .27 4.1.11 Temperature Sensor .22 4.1.12 L8 V Internal LDO Voltage Regulator .22 4.1.14 Comparators .23 4.1.15 Configurable Logic .33 4.1.16 Port I/O .33 4.1.17 SMBus .33			
3.9 Debugging .15 3.10 Bootloader .16 4. Electrical Specifications .16 4.1 Electrical Characteristics .18 4.1.1 Recommended Operating Conditions .16 4.1.2 Power Consumption .16 4.1.3 Reset and Supply Monitor .16 4.1.4 Flash Memory .21 4.1.5 Power Management Timing .22 4.1.6 Internal Oscillators .22 4.1.7 External Clock Input .22 4.1.8 External Oscillator .22 4.1.9 ADC .22 4.1.10 Voltage Reference .27 4.1.13 DACs .22 4.1.14 Comparators .22 4.1.15 Configurable Logic .33 4.1.16 Port I/O .32 4.1.18 SPI .35			
3.10 Bootloader			
4. Electrical Specifications 18 4.1 Electrical Characteristics 18 4.1.1 Recommended Operating Conditions 18 4.1.2 Power Consumption 19 4.1.3 Reset and Supply Monitor 21 4.1.4 Flash Memory 21 4.1.5 Power Management Timing 22 4.1.6 Internal Oscillators 22 4.1.7 External Clock Input 22 4.1.8 External Oscillator 22 4.1.9 ADC 22 4.1.10 Voltage Reference 22 4.1.11 Temperature Sensor 22 4.1.12 1.8 V Internal LDO Voltage Regulator 22 4.1.14 Comparators 33 4.1.15 Configurable Logic 33 4.1.16 Port I/O 33 4.1.18 SPI 35			
4.1 Electrical Characteristics 18 4.1.1 Recommended Operating Conditions 18 4.1.2 Power Consumption. 19 4.1.3 Reset and Supply Monitor. 21 4.1.4 Flash Memory. 21 4.1.5 Power Management Timing 22 4.1.6 Internal Oscillators 22 4.1.7 External Clock Input. 23 4.1.8 External Oscillator 22 4.1.10 Voltage Reference 27 4.1.11 Temperature Sensor 22 4.1.12 1.8 V Internal LDO Voltage Regulator 22 4.1.14 Comparators. 30 4.1.15 Configurable Logic. 31 4.1.16 Port I/O 32 4.1.17 SMBus. 33 4.1.18 SPI 35		3.10 Bootloader	16
4.1.1 Recommended Operating Conditions .18 4.1.2 Power Consumption. .19 4.1.3 Reset and Supply Monitor. .21 4.1.4 Flash Memory. .21 4.1.5 Power Management Timing .22 4.1.6 Internal Oscillators .22 4.1.7 External Clock Input. .22 4.1.8 External Oscillator .22 4.1.9 ADC .22 4.1.10 Voltage Reference. .22 4.1.11 Temperature Sensor .22 4.1.12 1.8 V Internal LDO Voltage Regulator .22 4.1.14 Comparators .22 4.1.15 Configurable Logic. .31 4.1.16 Port I/O .32 4.1.18 SPI .36	4.	Electrical Specifications	18
4.1.2 Power Consumption. .14 4.1.3 Reset and Supply Monitor. .21 4.1.4 Flash Memory. .21 4.1.5 Power Management Timing .22 4.1.6 Internal Oscillators .22 4.1.7 External Clock Input. .22 4.1.8 External Oscillator .22 4.1.9 ADC .22 4.1.10 Voltage Reference. .27 4.1.11 Temperature Sensor .22 4.1.12 1.8 V Internal LDO Voltage Regulator .22 4.1.14 Comparators. .30 4.1.15 Configurable Logic. .31 4.1.16 Port I/O .32 4.1.18 SPI .36		4.1 Electrical Characteristics	18
4.1.3 Reset and Supply Monitor. 21 4.1.4 Flash Memory. 21 4.1.5 Power Management Timing 22 4.1.6 Internal Oscillators 22 4.1.7 External Clock Input. 23 4.1.8 External Oscillator 23 4.1.9 ADC 22 4.1.10 Voltage Reference 27 4.1.11 Temperature Sensor 26 4.1.12 1.8 V Internal LDO Voltage Regulator 22 4.1.13 DACs 29 4.1.14 Comparators 30 4.1.15 Configurable Logic 31 4.1.16 Port I/O 32 4.1.18 SPI 35		4.1.1 Recommended Operating Conditions	18
4.1.4 Flash Memory		4.1.2 Power Consumption	19
4.1.5 Power Management Timing		4.1.3 Reset and Supply Monitor.	21
4.1.6 Internal Oscillators		4.1.4 Flash Memory	21
4.1.7 External Clock Input.		4.1.5 Power Management Timing	22
4.1.8 External Oscillator		4.1.6 Internal Oscillators	22
4.1.9 ADC		4.1.7 External Clock Input.	23
4.1.10 Voltage Reference		4.1.8 External Oscillator	23
4.1.11 Temperature Sensor		4.1.9 ADC	24
4.1.12 1.8 V Internal LDO Voltage Regulator		4.1.10 Voltage Reference	27
4.1.13 DACs		•	
4.1.14 Comparators			
4.1.15 Configurable Logic. .			
4.1.16 Port I/O . <		·	
4.1.17 SMBus			
4.1.18 SPI			
4.2 Thermal Conditions		4.1.18 SPI	35
		4.2 Thermal Conditions	38
4.3 Absolute Maximum Ratings		4.3 Absolute Maximum Ratings.	39
5. Typical Connection Diagrams	5.	Typical Connection Diagrams	40
5.1 Power			
5.2 Debug			
5.3 Other Connections.			

6.	Pin Definitions	•	•	•	•	•	•	•	• •	•	•	•	•	•	•	•	•	•	•	•	42
	6.1 EFM8LB1x-QFN32 Pin Definitions .																				.42
	6.2 EFM8LB1x-QFP32 Pin Definitions .																				.47
	6.3 EFM8LB1x-QFN24 Pin Definitions .																				.52
	6.4 EFM8LB1x-QSOP24 Pin Definitions.																				.57
7.	QFN32 Package Specifications																				62
	7.1 Package Dimensions																				.62
	7.2 PCB Land Pattern																				.64
	7.3 Package Marking														•						.65
8.	QFP32 Package Specifications																				66
	8.1 Package Dimensions																				.66
	8.2 PCB Land Pattern																				.68
	8.3 Package Marking													•							.69
9.	QFN24 Package Specifications																				70
	9.1 Package Dimensions																				.70
	9.2 PCB Land Pattern																				.72
	9.3 Package Marking																				.73
10	. QSOP24 Package Specifications																				.74
	10.1 Package Dimensions																				.74
	10.2 PCB Land Pattern																				.76
	10.3 Package Marking																				.77
11	. Revision History								•												78

3. System Overview

3.1 Introduction




Figure 3.1. Detailed EFM8LB1 Block Diagram

This section describes the EFM8LB1 family at a high level.

For more information on the device packages and pinout, electrical specifications, and typical connection diagrams, see the EFM8LB1 Data Sheet. For more information on each module including register definitions, see the EFM8LB1 Reference Manual. For more information on any errata, see the EFM8LB1 Errata.

3.2 Power

All internal circuitry draws power from the VDD supply pin. External I/O pins are powered from the VIO supply voltage (or VDD on devices without a separate VIO connection), while most of the internal circuitry is supplied by an on-chip LDO regulator. Control over the device power can be achieved by enabling/disabling individual peripherals as needed. Each analog peripheral can be disabled when not in use and placed in low power mode. Digital peripherals, such as timers and serial buses, have their clocks gated off and draw little power when they are not in use.

Table 3.1. Power Modes

Power Mode	Details	Mode Entry	Wake-Up Sources
Normal	Core and all peripherals clocked and fully operational		
ldle	 Core halted All peripherals clocked and fully operational Code resumes execution on wake event 	Set IDLE bit in PCON0	Any interrupt
Suspend	 Core and peripheral clocks halted HFOSC0 and HFOSC1 oscillators stopped Regulator in normal bias mode for fast wake Timer 3 and 4 may clock from LFOSC0 Code resumes execution on wake event 	 Switch SYSCLK to HFOSC0 Set SUSPEND bit in PCON1 	 Timer 4 Event SPI0 Activity I2C0 Slave Activity Port Match Event Comparator 0 Falling Edge CLUn Interrupt-Enabled Event
Stop	 All internal power nets shut down Pins retain state Exit on any reset source	1. Clear STOPCF bit in REG0CN 2. Set STOP bit in PCON0	Any reset source
Snooze	 Core and peripheral clocks halted HFOSC0 and HFOSC1 oscillators stopped Regulator in low bias current mode for energy savings Timer 3 and 4 may clock from LFOSC0 Code resumes execution on wake event 	 Switch SYSCLK to HFOSC0 Set SNOOZE bit in PCON1 	 Timer 4 Event SPI0 Activity I2C0 Slave Activity Port Match Event Comparator 0 Falling Edge CLUn Interrupt-Enabled Event
Shutdown	 All internal power nets shut down Pins retain state Exit on pin or power-on reset 	1. Set STOPCF bit in REG0CN 2. Set STOP bit in PCON0	RSTb pin resetPower-on reset

3.3 I/O

Digital and analog resources are externally available on the device's multi-purpose I/O pins. Port pins P0.0-P2.3 can be defined as general-purpose I/O (GPIO), assigned to one of the internal digital resources through the crossbar or dedicated channels, or assigned to an analog function. Port pins P2.4 to P3.7 can be used as GPIO. Additionally, the C2 Interface Data signal (C2D) is shared with P3.0 or P3.7, depending on the package option.

The port control block offers the following features:

- Up to 29 multi-function I/O pins, supporting digital and analog functions.
- Flexible priority crossbar decoder for digital peripheral assignment.
- Two drive strength settings for each port.
- State retention feature allows pins to retain configuration through most reset sources.
- Two direct-pin interrupt sources with dedicated interrupt vectors (INT0 and INT1).
- Up to 24 direct-pin interrupt sources with shared interrupt vector (Port Match).

3.4 Clocking

The CPU core and peripheral subsystem may be clocked by both internal and external oscillator resources. By default, the system clock comes up running from the 24.5 MHz oscillator divided by 8.

The clock control system offers the following features:

- · Provides clock to core and peripherals.
- 24.5 MHz internal oscillator (HFOSC0), accurate to ±2% over supply and temperature corners.
- 72 MHz internal oscillator (HFOSC1), accurate to ±2% over supply and temperature corners.
- 80 kHz low-frequency oscillator (LFOSC0).
- · External RC, and CMOS clock options (EXTCLK and EXTOSC).
- · Clock divider with eight settings for flexible clock scaling:
 - Divide the selected clock source by 1, 2, 4, 8, 16, 32, 64, or 128.
 - HFOSC0 and HFOSC1 include 1.5x pre-scalers for further flexibility.

3.5 Counters/Timers and PWM

Programmable Counter Array (PCA0)

The programmable counter array (PCA) provides multiple channels of enhanced timer and PWM functionality while requiring less CPU intervention than standard counter/timers. The PCA consists of a dedicated 16-bit counter/timer and one 16-bit capture/compare module for each channel. The counter/timer is driven by a programmable timebase that has flexible external and internal clocking options. Each capture/compare module may be configured to operate independently in one of five modes: Edge-Triggered Capture, Software Timer, High-Speed Output, Frequency Output, or Pulse-Width Modulated (PWM) Output. Each capture/compare module has its own associated I/O line (CEXn) which is routed through the crossbar to port I/O when enabled.

- · 16-bit time base
- Programmable clock divisor and clock source selection
- · Up to six independently-configurable channels
- 8, 9, 10, 11 and 16-bit PWM modes (center or edge-aligned operation)
- Output polarity control
- Frequency output mode
- · Capture on rising, falling or any edge
- · Compare function for arbitrary waveform generation
- · Software timer (internal compare) mode
- · Can accept hardware "kill" signal from comparator 0 or comparator 1

Timers (Timer 0, Timer 1, Timer 2, Timer 3, Timer 4, and Timer 5)

Several counter/timers are included in the device: two are 16-bit counter/timers compatible with those found in the standard 8051, and the rest are 16-bit auto-reload timers for timing peripherals or for general purpose use. These timers can be used to measure time intervals, count external events and generate periodic interrupt requests. Timer 0 and Timer 1 are nearly identical and have four primary modes of operation. The other timers offer both 16-bit and split 8-bit timer functionality with auto-reload and capture capabilities.

Timer 0 and Timer 1 include the following features:

- Standard 8051 timers, supporting backwards-compatibility with firmware and hardware.
- Clock sources include SYSCLK, SYSCLK divided by 12, 4, or 48, the External Clock divided by 8, or an external pin.
- · 8-bit auto-reload counter/timer mode
- · 13-bit counter/timer mode
- 16-bit counter/timer mode
- Dual 8-bit counter/timer mode (Timer 0)

Timer 2, Timer 3, Timer 4, and Timer 5 are 16-bit timers including the following features:

- · Clock sources for all timers include SYSCLK, SYSCLK divided by 12, or the External Clock divided by 8
- · LFOSC0 divided by 8 may be used to clock Timer 3 and Timer 4 in active or suspend/snooze power modes
- Timer 4 is a low-power wake source, and can be chained together with Timer 3
- 16-bit auto-reload timer mode
- Dual 8-bit auto-reload timer mode
- · External pin capture
- LFOSC0 capture
- Comparator 0 capture
- Configurable Logic output capture

Watchdog Timer (WDT0)

The device includes a programmable watchdog timer (WDT) running off the low-frequency oscillator. A WDT overflow forces the MCU into the reset state. To prevent the reset, the WDT must be restarted by application software before overflow. If the system experiences a software or hardware malfunction preventing the software from restarting the WDT, the WDT overflows and causes a reset. Following a reset, the WDT is automatically enabled and running with the default maximum time interval. If needed, the WDT can be disabled by system software or locked on to prevent accidental disabling. Once locked, the WDT cannot be disabled until the next system reset. The state of the RST pin is unaffected by this reset.

The Watchdog Timer has the following features:

- · Programmable timeout interval
- · Runs from the low-frequency oscillator
- · Lock-out feature to prevent any modification until a system reset

3.6 Communications and Other Digital Peripherals

Universal Asynchronous Receiver/Transmitter (UART0)

UART0 is an asynchronous, full duplex serial port offering modes 1 and 3 of the standard 8051 UART. Enhanced baud rate support allows a wide range of clock sources to generate standard baud rates. Received data buffering allows UART0 to start reception of a second incoming data byte before software has finished reading the previous data byte.

The UART module provides the following features:

- Asynchronous transmissions and receptions.
- Baud rates up to SYSCLK/2 (transmit) or SYSCLK/8 (receive).
- 8- or 9-bit data.
- Automatic start and stop generation.
- · Single-byte FIFO on transmit and receive.

Universal Asynchronous Receiver/Transmitter (UART1)

UART1 is an asynchronous, full duplex serial port offering a variety of data formatting options. A dedicated baud rate generator with a 16-bit timer and selectable prescaler is included, which can generate a wide range of baud rates. A received data FIFO allows UART1 to receive multiple bytes before data is lost and an overflow occurs.

UART1 provides the following features:

- · Asynchronous transmissions and receptions
- Dedicated baud rate generator supports baud rates up to SYSCLK/2 (transmit) or SYSCLK/8 (receive)
- 5, 6, 7, 8, or 9 bit data
- Automatic start and stop generation
- Automatic parity generation and checking
- · Single-byte buffer on transmit and receive
- Auto-baud detection
- · LIN break and sync field detection
- · CTS / RTS hardware flow control

Serial Peripheral Interface (SPI0)

The serial peripheral interface (SPI) module provides access to a flexible, full-duplex synchronous serial bus. The SPI can operate as a main (clock driver) or secondary (clock receiver) interface in both 3-wire or 4-wire modes, and supports multiple main/secondary devices on a single SPI bus. The chip-select (NSS) signal can be configured as an input to select the SPI in secondary mode, or to disable main mode operation in an environment with multiple main interfaces, avoiding contention on the SPI bus when more than one main device attempts simultaneous data transfers. NSS can also be configured as a firmware-controlled chip-select output in main inferface mode, or disabled to reduce the number of pins required. Additional general purpose port I/O pins can be used to select multiple secondary devices.

- · Supports 3- or 4-wire main or secondary modes
- · Supports external clock frequencies up to 12 Mbps in main or secondary mode
- · Support for all clock phase and polarity modes
- · 8-bit programmable clock rate (main)
- · Programmable receive timeout (secondary)
- · Two byte FIFO on transmit and receive
- · Can operate in suspend or snooze modes and wake the CPU on reception of a byte
- · Support for multiple mains on the same data lines

System Management Bus / I2C (SMB0)

The SMBus I/O interface is a two-wire, bi-directional serial bus. The SMBus is compliant with the System Management Bus Specification, version 1.1, and compatible with the I²C serial bus.

The SMBus module includes the following features:

- Standard (up to 100 kbps) and Fast (400 kbps) transfer speeds
- · Support for leader, follower, and multi-leader modes
- · Hardware synchronization and arbitration for multi-leader mode
- · Clock low extending (clock stretching) to interface with faster leader devices
- · Hardware support for 7-bit follower and general call address recognition
- · Firmware support for 10-bit follower address decoding
- · Ability to inhibit all follower states
- · Programmable data setup/hold times
- Transmit and receive FIFOs (one byte) to help increase throughput in faster applications

I2C Slave (I2CSLAVE0)

The I2C Slave interface is a 2-wire, bidirectional serial bus that is compatible with the I2C Bus Specification 3.0. It is capable of transferring in high-speed mode (HS-mode) at speeds of up to 3.4 Mbps. Firmware can write to the I2C interface, and the I2C interface can autonomously control the serial transfer of data. The interface also supports clock stretching for cases where the core may be temporarily prohibited from transmitting a byte or processing a received byte during an I2C transaction. This module operates only as an I2C slave device.

The I2C module includes the following features:

- Standard (up to 100 kbps), Fast (400 kbps), Fast Plus (1 Mbps), and High-speed (3.4 Mbps) transfer speeds
- · Support for slave mode only
- · Clock low extending (clock stretching) to interface with faster masters
- · Hardware support for 7-bit slave address recognition
- Transmit and receive FIFOs (two byte) to help increase throughput in faster applications
- · Hardware support for multiple slave addresses with the option to save the matching address in the receive FIFO

16-bit CRC (CRC0)

The cyclic redundancy check (CRC) module performs a CRC using a 16-bit polynomial. CRC0 accepts a stream of 8-bit data and posts the 16-bit result to an internal register. In addition to using the CRC block for data manipulation, hardware can automatically CRC the flash contents of the device.

The CRC module is designed to provide hardware calculations for flash memory verification and communications protocols. The CRC module supports the standard CCITT-16 16-bit polynomial (0x1021), and includes the following features:

- Support for CCITT-16 polynomial
- Byte-level bit reversal
- · Automatic CRC of flash contents on one or more 256-byte blocks
- · Initial seed selection of 0x0000 or 0xFFFF

Configurable Logic Units (CLU0, CLU1, CLU2, and CLU3)

The Configurable Logic block consists of multiple Configurable Logic Units (CLUs). CLUs are flexible logic functions which may be used for a variety of digital functions, such as replacing system glue logic, aiding in the generation of special waveforms, or synchronizing system event triggers.

- · Four configurable logic units (CLUs), with direct-pin and internal logic connections
- Each unit supports 256 different combinatorial logic functions (AND, OR, XOR, muxing, etc.) and includes a clocked flip-flop for synchronous operations
- · Units may be operated synchronously or asynchronously
- · May be cascaded together to perform more complicated logic functions
- · Can operate in conjunction with serial peripherals such as UART and SPI or timing peripherals such as timers and PCA channels
- · Can be used to synchronize and trigger multiple on-chip resources (ADC, DAC, Timers, etc.)
- · Asynchronous output may be used to wake from low-power states

3.7 Analog

14/12/10-Bit Analog-to-Digital Converter (ADC0)

The ADC is a successive-approximation-register (SAR) ADC with 14-, 12-, and 10-bit modes, integrated track-and hold and a programmable window detector. The ADC is fully configurable under software control via several registers. The ADC may be configured to measure different signals using the analog multiplexer. The voltage reference for the ADC is selectable between internal and external reference sources.

- Up to 20 external inputs
- · Single-ended 14-bit, 12-bit and 10-bit modes
- Supports an output update rate of up to 1 Msps in 12-bit mode
- Channel sequencer logic with direct-to-XDATA output transfers
- Operation in a low power mode at lower conversion speeds
- Asynchronous hardware conversion trigger, selectable between software, external I/O and internal timer and configurable logic sources
- Output data window comparator allows automatic range checking
- Support for output data accumulation
- Conversion complete and window compare interrupts supported
- Flexible output data formatting
- Includes a fully-internal fast-settling 1.65 V reference and an on-chip precision 2.4 / 1.2 V reference, with support for using the supply as the reference, an external reference and signal ground
- Integrated factory-calibrated temperature sensor

12-Bit Digital-to-Analog Converters (DAC0, DAC1, DAC2, DAC3)

The DAC modules are 12-bit Digital-to-Analog Converters with the capability to synchronize multiple outputs together. The DACs are fully configurable under software control. The voltage reference for the DACs is selectable between internal and external reference sources.

- Voltage output with 12-bit performance
- · Hardware conversion trigger, selectable between software, external I/O and internal timer and configurable logic sources
- Outputs may be configured to persist through reset and maintain output state to avoid system disruption
- Multiple DAC outputs can be synchronized together
- DAC pairs (DAC0 and 1 or DAC2 and 3) support complementary output waveform generation
- · Outputs may be switched between two levels according to state of configurable logic / PWM input trigger
- Flexible input data formatting
- · Supports references from internal supply, on-chip precision reference, or external VREF pin

Low Current Comparators (CMP0, CMP1)

An analog comparator is used to compare the voltage of two analog inputs, with a digital output indicating which input voltage is higher. External input connections to device I/O pins and internal connections are available through separate multiplexers on the positive and negative inputs. Hysteresis, response time, and current consumption may be programmed to suit the specific needs of the application.

The comparator includes the following features:

- · Up to 10 (CMP0) or 9 (CMP1) external positive inputs
- · Up to 10 (CMP0) or 9 (CMP1) external negative inputs
- · Additional input options:
 - Internal connection to LDO output
 - Direct connection to GND
 - Direct connection to VDD
 - Dedicated 6-bit reference DAC
- Synchronous and asynchronous outputs can be routed to pins via crossbar
- Programmable hysteresis between 0 and ±20 mV
- Programmable response time
- Interrupts generated on rising, falling, or both edges
- PWM output kill feature

3.8 Reset Sources

Reset circuitry allows the controller to be easily placed in a predefined default condition. On entry to this reset state, the following occur:

- The core halts program execution.
- · Module registers are initialized to their defined reset values unless the bits reset only with a power-on reset.
- · External port pins are forced to a known state.
- · Interrupts and timers are disabled.

All registers are reset to the predefined values noted in the register descriptions unless the bits only reset with a power-on reset. The contents of RAM are unaffected during a reset; any previously stored data is preserved as long as power is not lost. By default, the Port I/O latches are reset to 1 in open-drain mode, with weak pullups enabled during and after the reset. Optionally, firmware may configure the port I/O, DAC outputs, and precision reference to maintain state through system resets other than power-on resets. For Supply Monitor and power-on resets, the RSTb pin is driven low until the device exits the reset state. On exit from the reset state, the program counter (PC) is reset, and the system clock defaults to an internal oscillator. The Watchdog Timer is enabled, and program execution begins at location 0x0000.

Reset sources on the device include the following:

- Power-on reset
- External reset pin
- Comparator reset
- · Software-triggered reset
- Supply monitor reset (monitors VDD supply)
- · Watchdog timer reset
- · Missing clock detector reset
- · Flash error reset

3.9 Debugging

The EFM8LB1 devices include an on-chip Silicon Labs 2-Wire (C2) debug interface to allow flash programming and in-system debugging with the production part installed in the end application. The C2 interface uses a clock signal (C2CK) and a bi-directional C2 data signal (C2D) to transfer information between the device and a host system. See the C2 Interface Specification for details on the C2 protocol.

3.10 Bootloader

All devices come pre-programmed with a UART0 bootloader or an SMBus bootloader. These bootloaders reside in the code security page, which is the last page of code flash; they can be erased if they are not needed.

The byte before the Lock Byte is the Bootloader Signature Byte. Setting this byte to a value of 0xA5 indicates the presence of the bootloader in the system. Any other value in this location indicates that the bootloader is not present in flash.

When a bootloader is present, the device will jump to the bootloader vector after any reset, allowing the bootloader to run. The bootloader then determines if the device should stay in bootload mode or jump to the reset vector located at 0x0000. When the bootloader is not present, the device will jump to the reset vector of 0x0000 after any reset.

Silicon Labs recommends the bootloader be disabled and the flash memory locked after the production programming step in applications where code security is a concern. More information about the factory bootloader protocol, usage, customization and best practices can be found in *AN945: EFM8 Factory Bootloader User Guide*. Application notes can be found on the Silicon Labs website (www.silabs.com/8bit-appnotes) or within Simplicity Studio by using the [**Application Notes**] tile.




Figure 3.2. Flash Memory Map with Bootloader — 62.5 KB Devices

Table 3.2.	Summary	of Pins for Bootloader	Communication
------------	---------	------------------------	---------------

Bootloader	Pins for Bootload Communication
UART	TX – P0.4
	RX – P0.5

Pins for Bootload Communication
P0.2 – SDA ¹
P0.3 – SCL ¹
P0.2 – SDA ¹
P0.4 – SCL ¹

Note:

1. The STK uses these pins for another purpose, so there is a special SMBus bootloader build for the STK only included in AN945: EFM8 Factory Bootloader User Guide that uses P1.2 (SDA) and P1.3 (SCL).

Table 3.3. Summary of Pins for Bootload Mode Entry

Device Package	Pin for Bootload Mode Entry							
QFN32	P3.7 / C2D							
QFP32	P3.7 / C2D							
QFN24	P3.0 / C2D							
QSOP24	P3.0 / C2D							

4. Electrical Specifications

4.1 Electrical Characteristics

All electrical parameters in all tables are specified under the conditions listed in Table 4.1 Recommended Operating Conditions on page 18, unless stated otherwise.

Table 4.1. Recommended Operating Conditions

4.1.1 Recommended Operating Conditions

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
Operating Supply Voltage on VDD	V _{DD}		2.2	_	3.6	V
Operating Supply Voltage on VIO ^{2,}	V _{IO}		2.2	_	V _{DD}	V
3			1.71 ³	—	V _{DD}	V
System Clock Frequency	f _{SYSCLK}		0	_	73.5	MHz
Operating Ambient Temperature	T _A		-40	_	105	°C

Note:

1. All voltages with respect to GND

2. In certain package configurations, the VIO and VDD supplies are bonded to the same pin.

3. I/O have reduced current drive/sink capabilities at lower VIO levels. See 4.1.16 Port I/O for additional information.

4.1.2 Power Consumption

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Digital Core Supply Current			1			
Normal Mode-Full speed with code	I _{DD}	F _{SYSCLK} = 72 MHz (HFOSC1) ²	_	12.9	15	mA
executing from flash		F _{SYSCLK} = 24.5 MHz (HFOSC0) ²	—	4.2	5	mA
		F _{SYSCLK} = 1.53 MHz (HFOSC0) ²	—	625	1050	μA
		F _{SYSCLK} = 80 kHz ³	—	155	575	μA
dle Mode-Core halted with periph-	I _{DD}	F _{SYSCLK} = 72 MHz (HFOSC1) ²	—	9.6	11.1	mA
erals running		F _{SYSCLK} = 24.5 MHz (HFOSC0) ²	—	3.14	3.8	mA
		F _{SYSCLK} = 1.53 MHz (HFOSC0) ²	—	520	950	μA
		F _{SYSCLK} = 80 kHz ³	—	135	550	μA
Suspend Mode-Core halted and	I _{DD}	LFO Running	_	125	545	μA
high frequency clocks stopped, Supply monitor off.		LFO Stopped	—	120	535	μA
Snooze Mode-Core halted and	I _{DD}	LFO Running	_	23	430	μA
high frequency clocks stopped. Regulator in low-power state, Sup- ply monitor off.		LFO Stopped		19	425	μA
Stop Mode—Core halted and all clocks stopped,Internal LDO On, Supply monitor off.	I _{DD}		_	120	535	μA
Shutdown Mode—Core halted and all clocks stopped,Internal LDO Off, Supply monitor off.	IDD		_	0.2	2.1	μA
Analog Peripheral Supply Current	ts					
High-Frequency Oscillator 0	I _{HFOSC0}	Operating at 24.5 MHz,	_	120	135	μA
		T _A = 25 °C				
High-Frequency Oscillator 1	I _{HFOSC1}	Operating at 72 MHz,	—	1285	1340	μA
		T _A = 25 °C				
Low-Frequency Oscillator	I _{LFOSC}	Operating at 80 kHz,	—	3.7	6	μA
		T _A = 25 °C				

Table 4.2. Power Consumption

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
ADC0 ⁴	I _{ADC}	High Speed Mode		1275	1700	μA
		1 Msps, 12-bit conversions				
		Normal bias settings				
		V _{DD} = 3.0 V				
		Low Power Mode	_	390	530	μA
		350 ksps, 12-bit conversions				
		Low power bias settings				
		V _{DD} = 3.0 V				
Internal ADC0 Reference ⁵	I _{VREFFS}	High Speed Mode	_	700	790	μA
		Low Power Mode	_	170	210	μA
On-chip Precision Reference	I _{VREFP}		_	75	_	μA
Temperature Sensor	ITSENSE		_	68	120	μA
Digital-to-Analog Converters (DAC0, DAC1, DAC2, DAC3) ⁶	I _{DAC}		_	125	_	μA
Comparators (CMP0, CMP1)	I _{CMP}	CPMD = 11	_	0.5	_	μA
		CPMD = 10	_	3	_	μA
		CPMD = 01	_	10	—	μA
		CPMD = 00	—	25	—	μA
Comparator Reference ⁷	I _{CPREF}		_	24	—	μA
Voltage Supply Monitor (VMON0)	I _{VMON}		_	15	20	μA

Note:

1. Currents are additive. For example, where I_{DD} is specified and the mode is not mutually exclusive, enabling the functions increases supply current by the specified amount.

- 2. Includes supply current from internal LDO regulator, supply monitor, and High Frequency Oscillator.
- 3. Includes supply current from internal LDO regulator, supply monitor, and Low Frequency Oscillator.
- 4. ADC0 power excludes internal reference supply current.
- 5. The internal reference is enabled as-needed when operating the ADC in low power mode. Total ADC + Reference current will depend on sampling rate.
- 6. DAC supply current for each enabled DA and not including external load on pin.

7. This value is the current sourced from the pin or supply selected as the full-scale reference to the comparator DAC.

4.1.3 Reset and Supply Monitor

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
VDD Supply Monitor Threshold	V _{VDDM}		1.95	2.05	2.15	V
Power-On Reset (POR) Threshold	V _{POR}	Rising Voltage on VDD	_	1.4	_	V
		Falling Voltage on VDD	0.75		1.36	V
VDD Ramp Time	t _{RMP}	Time to V _{DD} > 2.2 V	10	_	_	μs
Reset Delay from POR	t _{POR}	Relative to V _{DD} > V _{POR}	3	10	31	ms
Reset Delay from non-POR source	t _{RST}	Time between release of reset source and code execution	_	50		μs
RST Low Time to Generate Reset	t _{RSTL}		15			μs
Missing Clock Detector Response Time (final rising edge to reset)	t _{MCD}	F _{SYSCLK} >1 MHz	_	0.625	1.2	ms
Missing Clock Detector Trigger Frequency	F _{MCD}		_	7.5	13.5	kHz
VDD Supply Monitor Turn-On Time	t _{MON}		_	2	—	μs

Table 4.3. Reset and Supply Monitor

4.1.4 Flash Memory

Table 4.4. Flash Memory

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
Write Time ^{1,2}	t _{WRITE}	One Byte,	19	20	21	μs
		F _{SYSCLK} = 24.5 MHz				
Erase Time ^{1 ,2}	t _{ERASE}	One Page,	5.2	5.35	5.5	ms
		F _{SYSCLK} = 24.5 MHz				
V _{DD} Voltage During Programming ³	V _{PROG}		2.2	_	3.6	V
Endurance (Write/Erase Cycles)	N _{WE}		20k	100k	_	Cycles
CRC Calculation Time	t _{CRC}	One 256-Byte Block	—	5.5	_	μs
		SYSCLK = 48 MHz				

Note:

1. Does not include sequencing time before and after the write/erase operation, which may be multiple SYSCLK cycles.

- 2. The internal High-Frequency Oscillator 0 has a programmable output frequency, which is factory programmed to 24.5 MHz. If user firmware adjusts the oscillator speed, it must be between 22 and 25 MHz during any flash write or erase operation. It is recommended to write the HFO0CAL register back to its reset value when writing or erasing flash.
- 3. Flash can be safely programmed at any voltage above the supply monitor threshold (V_{VDDM}).

4. Data Retention Information is published in the Quarterly Quality and Reliability Report.

4.1.5 Power Management Timing

Table 4.5. Power Management Timing

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
Idle Mode Wake-up Time	t _{IDLEWK}		2	_	3	SYSCLKs
Suspend Mode Wake-up Time	t _{SUS-}	SYSCLK = HFOSC0	—	170	_	ns
	PENDWK	CLKDIV = 0x00				
Snooze Mode Wake-up Time	t _{SLEEPWK}	SYSCLK = HFOSC0		12		μs
		CLKDIV = 0x00				

4.1.6 Internal Oscillators

Table 4.6. Internal Oscillators

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
High Frequency Oscillator 0	(24.5 MHz)					
Oscillator Frequency	f _{HFOSC0}	Full Temperature and Supply Range	24	24.5	25	MHz
Power Supply Sensitivity	PSS _{HFOS} C0	T _A = 25 °C	-	0.5	_	%/V
Temperature Sensitivity	TS _{HFOSC0}	V _{DD} = 3.0 V	_	40	_	ppm/°C
High Frequency Oscillator 1	(72 MHz)				1	
Oscillator Frequency	f _{HFOSC1}	Full Temperature and Supply Range	70.5	72	73.5	MHz
Power Supply Sensitivity	PSS _{HFOS} C1	T _A = 25 °C	_	300	_	ppm/V
Temperature Sensitivity	TS _{HFOSC1}	V _{DD} = 3.0 V	_	103	_	ppm/°C
Low Frequency Oscillator (80) kHz)				1	1
Oscillator Frequency	f _{LFOSC}	Full Temperature and Supply Range	75	80	85	kHz
Power Supply Sensitivity	PSS _{LFOSC}	T _A = 25 °C		0.05	_	%/V
Temperature Sensitivity	TS _{LFOSC}	V _{DD} = 3.0 V	_	65		ppm/°C

4.1.7 External Clock Input

Table 4.7. External Clock Input

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
External Input CMOS Clock	f _{CMOS}		0	_	50	MHz
Frequency (at EXTCLK pin)						
External Input CMOS Clock High Time	t _{CMOSH}		9	_	_	ns
External Input CMOS Clock Low Time	t _{CMOSL}		9	_	_	ns

4.1.8 External Oscillator

Table 4.8. External Oscillator

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Frequency	f EXTOSC	XFCN = 000	0.02	_	25	kHz
		XFCN = 001	25	_	50	kHz
		XFCN = 010	50	—	100	kHz
		XFCN = 011	100	_	200	kHz
		XFCN = 100	200	—	400	kHz
		XFCN = 101	400	_	800	kHz
		XFCN = 110	800	_	1600	kHz
		XFCN = 111	1.6	_	3.2	MHz

Table 4.9. ADC

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit	
Resolution	N _{bits}	14 Bit Mode		14		Bits	
		12 Bit Mode		12			
		10 Bit Mode		10		Bits	
Throughput Rate	f _S	14 Bit Mode	_		900	ksps	
(High Speed Mode)		12 Bit Mode	_	_	1	Msps	
		10 Bit Mode	_		1.125	Msps	
Throughput Rate	f _S	14 Bit Mode	_	_	320	ksps	
(Low Power Mode)		12 Bit Mode	_	_	340	ksps	
		10 Bit Mode	_	_	360	ksps	
Tracking Time	t _{TRK}	High Speed Mode	217.8 ¹	—	_	ns	
		Low Power Mode	450		_	ns	
Power-On Time	t _{PWR}		1.2		_	μs	
SAR Clock Frequency	f _{SAR}	High Speed Mode	_	_	18.36	MHz	
		Low Power Mode	_		12.25	MHz	
Conversion Time ²	t _{CNV}	14-Bit Conversion,		0.81		μs	
		SAR Clock =18 MHz,					
		System Clock = 72 MHz.					
		12-Bit Conversion,		0.7		μs	
		SAR Clock =18 MHz,					
		System Clock = 72 MHz.					
		10-Bit Conversion,		0.59		μs	
		SAR Clock =18 MHz,					
		System Clock = 72 MHz.					
Sample/Hold Capacitor	C _{SAR}	Gain = 1	_	5.2	_	pF	
		Gain = 0.75	_	3.9	_	pF	
		Gain = 0.5	_	2.6	_	pF	
		Gain = 0.25	_	1.3	_	pF	
Input Pin Capacitance	C _{IN}	High Quality Input	_	20	_	pF	
		Normal Input		20	_	pF	
Input Mux Impedance	R _{MUX}	High Quality Input	-	330	_	Ω	
		Normal Input	-	550	_	Ω	
Voltage Reference Range	V _{REF}		1	_	V _{IO}	V	
Input Voltage Range ³	V _{IN}		0		V _{REF} / Gain	V	

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Power Supply Rejection Ratio	PSRR _{ADC}	At 1 kHz	_	66		dB
		At 1 MHz	_	43	_	dB
DC Performance	·					
Integral Nonlinearity	INL	14 Bit Mode	-3.5 ⁴	-1.2 / +5	8.5 ⁴	LSB
		12 Bit Mode	-1.9	-0.35 / +1	1.9	LSB
		10 Bit Mode	-0.6	±0.2	0.6	LSB
Differential Nonlinearity (Guaran-	DNL	14 Bit Mode	-1 ⁴	±1	2.5 ⁴	LSB
teed Monotonic)		12 Bit Mode	-0.9	±0.3	0.9	LSB
		10 Bit Mode	-0.5	±0.2	0.5	LSB
Offset Error ⁵	E _{OFF}	14 Bit Mode	-8 ⁴	-2.5	8 ⁴	LSB
		12 Bit Mode	-2	0	2	LSB
		10 Bit Mode	-1	0	1	LSB
Offset Temperature Coefficient	TC _{OFF}		_	0.011		LSB/°C
Slope Error	E _M	14 Bit Mode	-15 ⁴	_	15 ⁴	LSB
		12 Bit Mode	-2.6	_	2.6	LSB
		10 Bit Mode	-1.1	_	1.1	LSB
Dynamic Performance 10 kHz Si	ne Wave Inp	ut 1 dB below full scale, Max throug	ghput, using	g AGND pin		1
Signal-to-Noise	SNR	14 Bit Mode	66 ⁴	72	_	dB
		12 Bit Mode	64	68	_	dB
		10 Bit Mode	59	61	—	dB
Signal-to-Noise Plus Distortion	SNDR	14 Bit Mode	66 ⁴	72		dB
		12 Bit Mode	64	68	_	dB
		10 Bit Mode	59	61	—	dB
Total Harmonic Distortion (Up to	THD	14 Bit Mode	_	-74	_	dB
5th Harmonic)		12 Bit Mode	_	-72		dB
		10 Bit Mode	_	-69	_	dB
Spurious-Free Dynamic Range	SFDR	14 Bit Mode	_	74		dB
		12 Bit Mode	_	74		dB
		10 Bit Mode	_	71	_	dB

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
Note:						
1. This time is equivalent to four p	eriods of a c	lock running at 18 MHz + 2%.				
2. Conversion Time does not inclu	de Tracking	Time. Total Conversion Time is:				
		+ NUMBITS + 1) x T(SARCLK)] +			1. I.C II A	
		presented by the ADRPT field and AE	DCCLK is the	e clock selec	ted for the A	DC.
3. Absolute input pin voltage is lim	lited by the V	/ _{IO} supply.				
4. Measured with characterization	data and no	t production tested.				
 The offset is determined using on positive. 	curve fitting s	since the specification is measured us	sing linear se	arch where t	the intercept	is always
6. Production test uses a 2.4 V ex	ternal refere	nce and external ground.				

4.1.10 Voltage Reference

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
Internal Fast Settling Reference						
Output Voltage	V _{REFFS}		1.62	1.65	1.68	V
(Full Temperature and Supply Range)						
Temperature Coefficient	TC _{REFFS}		_	50	_	ppm/°C
Turn-on Time	t _{REFFS}		_	—	1.5	μs
Power Supply Rejection	PSRR _{REF} FS		_	400	_	ppm/V
On-chip Precision Reference					1	1
Valid Supply Range	V _{DD}	1.2 V Output	2.2		3.6	V
		2.4 V Output	2.7	_	3.6	V
Output Voltage	V _{REFP}	1.2 V Output, V _{DD} = 3.3 V, T = 25 °C	1.195	1.2	1.205	V
		1.2 V Output	1.18	1.2	1.22	V
		2.4 V Output, V _{DD} = 3.3 V, T = 25 °C	2.39	2.4	2.41	V
		2.4 V Output	2.36	2.4	2.44	V
Turn-on Time, settling to 0.5 LSB	t _{VREFP}	4.7 μF tantalum + 0.1 μF ceramic bypass on VREF pin	_	3	_	ms
		0.1 µF ceramic bypass on VREF pin	—	100	_	μs
Load Regulation	LR _{VREFP}	VREF = 2.4 V, Load = 0 to 200 μ A to GND	—	8	_	μV/μΑ
		VREF = 1.2 V, Load = 0 to 200 μA to GND	_	5	_	μV/μΑ
Load Capacitor	C _{VREFP}	Load = 0 to 200 µA to GND	0.1	_	—	μF
Short-circuit current	ISC _{VREFP}		_		8	mA
Power Supply Rejection	PSRR _{VRE}			75	_	dB
External Reference	-	1		1		
Input Current	I _{EXTREF}	ADC Sample Rate = 1 Msps; VREF = 3.0 V	_	5		μA

4.1.11 Temperature Sensor

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Uncalibrated Offset	V _{OFF}	T _A = 0 °C	_	751	_	mV
Uncalibrated Offset Error ¹	E _{OFF}	T _A = 0 °C		19		mV
Slope	М			2.82	_	mV/°C
Slope Error ¹	E _M		_	29	_	µV/°C
Linearity	LIN	T = 0 °C to 70 °C	_	-0.1 to 0.15	_	°C
		T = -20 °C to 85 °C	_	-0.2 to 0.35	_	°C
		T = -40 °C to 105 °C	_	-0.4 to 0.8		°C
Turn-on Time	t _{ON}		_	3.5	_	μs
Temp Sensor Error Using Typical	E _{TOT}	T = 0 °C to 70 °C	-2.6	_	1.8	°C
Slope and Factory-Calibrated Off- set ^{2, 3}		T = -20 °C to 85 °C	-2.9	_	2.7	°C
		T = -40 °C to 105 °C	-3.2	_	4.2	°C

Table 4.11. Temperature Sensor

Note:

1. Represents one standard deviation from the mean.

2. The factory-calibrated offset value is stored in the read-only area of flash in locations 0xFFD4 (low byte) and 0xFFD5 (high byte). The 14-bit result represents the output of the ADC when sampling the temp sensor using the 1.65 V internal voltage reference.

3. The temp sensor error includes the offset calibration error, slope error, and linearity error. The values are based upon characterization and are not tested across temperature in production. The values represent three standard deviations above and below the mean. Additional information on achieving high measurement accuracy is available in AN929: Accurate Temperature Sensing with the EFM8 Laser Bee MCU Family.

4.1.12 1.8 V Internal LDO Voltage Regulator

Table 4.12. 1.8V Internal LDO Voltage Regulator

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
Output Voltage	V _{OUT_1.8V}		1.79	1.84	1.88	V

Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
Output Voltage	V _{OUT}		0	—	V _{DD}	V
Output Current	I _{OUT}		-2	_	2	mA
Resolution	N _{bits}			12	1	Bits
Throughput Rate	f _S		_	_	200	ksps
Integral Nonlinearity	INL	DAC0 and DAC2	-10	-1.77 / 1.56	10	LSB
		DAC1 and DAC3	-11.5	-2.73 / 1.11	11.5	LSB
Differential Nonlinearity	DNL		-1	_	1	LSB
Output Noise	V _{NOISE}	VREF = 2.4 V	—	110	_	μV _{RMS}
		f _S = 0.1 Hz to 300 kHz				
Slew Rate	SLEW			±1	_	V/µs
Output Settling Time to 1% Full- scale	^t SETTLE	V _{OUT} change between 25% and 75% Full Scale		2.6	5	μs
Power-on Time	t _{PWR}			_	10	μs
Voltage Reference Range	V _{REF}		1.15	_	V _{DD}	V
Power Supply Rejection Ratio	PSRR	DC, V _{OUT} = 50% Full Scale		78		dB
Total Harmonic Distortion	THD	V _{OUT} = 10 kHz sine wave, 10% to 90%	54	_		dB
Offset Error	E _{OFF}	VREF = 2.4 V	-8	0	8	LSB
Full-Scale Error	E _{FS}	VREF = 2.4 V	-13	±5	13	LSB
External Load Impedance	R _{LOAD}		2	-		kΩ
External Load Capacitance ¹	C _{LOAD}			_	100	pF
Load Regulation		V _{OUT} = 50% Full Scale	_	100	1300	µV/mA
		I _{OUT} = -2 to 2 mA				

Note:

1. No minimum external load capacitance is required. However, under low loading conditions, it is possible for the DAC output to glitch during start-up. If smooth start-up is required, the minimum loading capacitance at the pin should be a minimum of 10 pF.

4.1.14 Comparators

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Response Time, CPMD = 00	t _{RESP0}	+100 mV Differential		100	_	ns
(Highest Speed)		-100 mV Differential	_	150	_	ns
Response Time, CPMD = 11 (Low-	t _{RESP3}	+100 mV Differential	_	1.5	_	μs
est Power)		-100 mV Differential	_	3.5	_	μs
Positive Hysteresis	HYS _{CP+}	CPHYP = 00	_	0.4	_	mV
Mode 0 (CPMD = 00)		CPHYP = 01	_	8	_	mV
		CPHYP = 10	_	16	_	mV
		CPHYP = 11	_	32	_	mV
Negative Hysteresis	HYS _{CP-}	CPHYN = 00	_	-0.4	_	mV
Mode 0 (CPMD = 00)		CPHYN = 01	_	-8	_	mV
		CPHYN = 10	_	-16	_	mV
		CPHYN = 11	_	-32	_	mV
Positive Hysteresis	HYS _{CP+}	CPHYP = 00	_	0.5	_	mV
Mode 1 (CPMD = 01)		CPHYP = 01	_	6	_	mV
		CPHYP = 10	_	12	_	mV
		CPHYP = 11	_	24	_	mV
Negative Hysteresis	HYS _{CP-}	CPHYN = 00	_	-0.5	_	mV
Mode 1 (CPMD = 01)		CPHYN = 01	_	-6	_	mV
		CPHYN = 10	_	-12	_	mV
		CPHYN = 11	_	-24	_	mV
Positive Hysteresis	HYS _{CP+}	CPHYP = 00	_	0.7	_	mV
Mode 2 (CPMD = 10)		CPHYP = 01	_	4.5	_	mV
		CPHYP = 10	_	9	_	mV
		CPHYP = 11	_	18	_	mV
Negative Hysteresis	HYS _{CP-}	CPHYN = 00	_	-0.6	_	mV
Mode 2 (CPMD = 10)		CPHYN = 01	_	-4.5	_	mV
		CPHYN = 10	_	-9	_	mV
		CPHYN = 11	_	-18	_	mV
Positive Hysteresis	HYS _{CP+}	CPHYP = 00	_	1.5	_	mV
Mode 3 (CPMD = 11)		CPHYP = 01		4	_	mV
		CPHYP = 10	_	8	_	mV
		CPHYP = 11		16	_	mV

Table 4.14. Comparators

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Negative Hysteresis	HYS _{CP-}	CPHYN = 00	—	-1.5	_	mV
Mode 3 (CPMD = 11)		CPHYN = 01	—	-4	_	mV
		CPHYN = 10	_	-8	_	mV
		CPHYN = 11	—	-16	—	mV
Input Range (CP+ or CP-)	V _{IN}		-0.25	_	V _{IO} +0.25	V
Input Pin Capacitance	C _{CP}		—	7.5	—	pF
Internal Reference DAC Resolution	N _{bits}			6	1	bits
Common-Mode Rejection Ratio	CMRR _{CP}		_	70	_	dB
Power Supply Rejection Ratio	PSRR _{CP}		—	72	_	dB
Input Offset Voltage	V _{OFF}	T _A = 25 °C	-10	0	10	mV
Input Offset Tempco	TC _{OFF}		_	3.5	—	μV/°

4.1.15 Configurable Logic

Table 4.15. Configurable Logic

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Propagation Delay	t _{DLY}	Through single CLU	_	_	35.3	ns
		Using an external pin				
		Through single CLU	—	3	—	ns
		Using an internal connection				
Clocking Frequency	F _{CLK}	1 or 2 CLUs Cascaded	—	—	73.5	MHz
		3 or 4 CLUs Cascaded			36.75	MHz

4.1.16 Port I/O

Table 4.16. Port I/O

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Output High Voltage (High Drive)	V _{OH}	I _{OH} = -7 mA, V _{IO} ≥ 3.0 V	V _{IO} - 0.7	_	—	V
		I_{OH} = -3.3 mA, 2.2 V ≤ V _{IO} < 3.0 V	V _{IO} x 0.8		_	V
		I _{OH} = -1.8 mA, 1.71 V ≤ V _{IO} < 2.2 V				
Output Low Voltage (High Drive)	V _{OL}	I _{OL} = 13.5 mA, V _{IO} ≥ 3.0 V	_	_	0.6	V
		I_{OL} = 7 mA, 2.2 V ≤ V_{IO} < 3.0 V	_	_	V _{IO} x 0.2	V
		I_{OL} = 3.6 mA, 1.71 V ≤ V_{IO} < 2.2 V				
Output High Voltage (Low Drive)	V _{OH}	I _{OH} = -4.75 mA, V _{IO} ≥ 3.0 V	V _{IO} - 0.7	_	_	V
		I_{OH} = -2.25 mA, 2.2 V ≤ V _{IO} < 3.0 V	V _{IO} x 0.8		_	V
		I_{OH} = -1.2 mA, 1.71 V \leq V _{IO} < 2.2 V				
Output Low Voltage (Low Drive)	V _{OL}	I _{OL} = 6.5 mA, V _{IO} ≥ 3.0 V	_	_	0.6	V
		I_{OL} = 3.5 mA, 2.2 V ≤ V_{IO} < 3.0 V	_	_	V _{IO} x 0.2	V
		I_{OL} = 1.8 mA, 1.71 V \leq V _{IO} < 2.2 V				
Input High Voltage	V _{IH}		0.7 x	_	_	V
			V _{IO}			
Input Low Voltage	V _{IL}		—	_	0.3 x	V
					V _{IO}	
Pin Capacitance	C _{IO}		—	7	—	pF
Weak Pull-Up Current	I _{PU}	V _{DD} = 3.6	-30	-20	-10	μA
(V _{IN} = 0 V)						
Input Leakage (Pullups off or Ana- log)	I _{LK}	GND < V _{IN} < V _{IO}	-1.1	_	4	μA
Input Leakage Current with VIN	I _{LK}	V _{IO} < V _{IN} < V _{IO} +2.5 V	0	5	150	μA
above V _{IO}		Any pin except P3.0, P3.1, P3.2, or P3.3				

4.1.17 SMBus

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Standard Mode (100 kHz Class)	1				1	
I2C Operating Frequency	f _{I2C}		0	_	70 ²	kHz
SMBus Operating Frequency	f _{SMB}		40 ¹	_	70 ²	kHz
Bus Free Time Between STOP and START Conditions	t _{BUF}		9.4	_	_	μs
Hold Time After (Repeated) START Condition	t _{HD:STA}		4.7		_	μs
Repeated START Condition Setup Time	t _{SU:STA}		9.4	_	_	μs
STOP Condition Setup Time	t _{su:sтo}		9.4		_	μs
Data Hold Time	t _{HD:DAT}		275 ³		_	ns
Data Setup Time	t _{SU:DAT}		300 ³		_	ns
Detect Clock Low Timeout	t _{TIMEOUT}		25		_	ms
Clock Low Period	t _{LOW}		4.7		_	μs
Clock High Period	t _{HIGH}		9.4	_	50 ⁴	μs
Fast Mode (400 kHz Class)		1				
I2C Operating Frequency	f _{I2C}		0	_	256 ²	kHz
SMBus Operating Frequency	f _{SMB}		40 ¹	_	256 ²	kHz
Bus Free Time Between STOP and START Conditions	t _{BUF}		2.6		_	μs
Hold Time After (Repeated) START Condition	t _{HD:STA}		1.3		_	μs
Repeated START Condition Setup Time	t _{SU:STA}		2.6	_	_	μs
STOP Condition Setup Time	t _{su:sтo}		2.6		-	μs
Data Hold Time	t _{HD:DAT}		275 ³	_	—	ns
Data Setup Time	t _{SU:DAT}		300 ³		_	ns
Detect Clock Low Timeout	t _{TIMEOUT}		25		_	ms
Clock Low Period	t _{LOW}		1.3		_	μs
Clock High Period	t _{HIGH}		2.6		50 ⁴	μs

Table 4.17. SMBus Peripheral Timing Performance (Master Mode)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit		
Note:								
1. The minimum SMBus frequency	y is limited b	y the maximum Clock High Period rec	quirement of	the SMBus s	specification.			

2. The maximum I2C and SMBus frequencies are limited by the minimum Clock Low Period requirements of their respective specifications.

3. Data setup and hold timing at 40 MHz or lower with EXTHOLD set to 1. The DLYEXT bit can be used to adjust the data setup and hold times.

Table 4.18. SMBus Peripheral Timing Formulas (Master Mode)

Parameter	Symbol	Clocks
SMBus Operating Frequency	f _{SMB}	f _{CSO} / 3
Bus Free Time Between STOP and START Conditions	t _{BUF}	2 / f _{CSO}
Hold Time After (Repeated) START Condition	t _{HD:STA}	1 / f _{CSO}
Repeated START Condition Setup Time	t _{SU:STA}	2 / f _{CSO}
STOP Condition Setup Time	t _{SU:STO}	2 / f _{CSO}
Clock Low Period	t _{LOW}	1 / f _{CSO}
Clock High Period	tнідн	2 / f _{CSO}
Note:		1

 $1.\,f_{CSO}$ is the SMBus peripheral clock source overflow frequency.





Figure 4.1. SMBus Peripheral Timing Diagram (Master Mode)


^{4.} SMBus has a maximum requirement of 50 μs for Clock High Period. Operating frequencies lower than 40 kHz will be longer than 50 μs. I2C can support periods longer than 50 μs.


Table 4.19.	SPI	Timing	Parameters
-------------	-----	--------	------------

Parameter	Description	Min	Мах	Units
ster Mode Timi	ng			
Т _{МСКН}	SCK High Time	$\frac{1}{2 \times 12 \text{ MHz}}$	_	ns
T _{MCKL}	SCK Low Time	$\frac{1}{2 \times 12 \text{ MHz}}$	_	ns
T _{MIS}	MISO Valid to SCK Sample Edge	20	_	ns
Т _{МІН}	SCK Sample Edge to MISO Change	5		ns
ave Mode Timin	g			
T _{SE}	NSS Falling to First SCK Edge	5	_	ns
T _{SD}	Last SCK Edge to NSS Rising	5	_	ns
T _{SEZ}	NSS Falling to MISO Valid	_	20	ns
T _{SDZ}	NSS Rising to MISO High-Z	_	20	ns
Т _{СКН}	SCK High Time	40	_	ns
T _{CKL}	SCK Low Time	40	_	ns
T _{SIS}	MOSI Valid to SCK Sample Edge	20	_	ns
T _{SIH}	SCK Sample Edge to MOSI Change	5	_	ns
Т _{SOH}	SCK Shift Edge to MISO Change	_	20	ns




* SCK is shown for CKPOL = 0. SCK is the opposite polarity for CKPOL = 1.






* SCK is shown for CKPOL = 0. SCK is the opposite polarity for CKPOL = 1.

Figure 4.3. SPI Master Timing (CKPHA = 1)



* SCK is shown for CKPOL = 0. SCK is the opposite polarity for CKPOL = 1.





* SCK is shown for CKPOL = 0. SCK is the opposite polarity for CKPOL = 1.



4.2 Thermal Conditions

QFN24 Packages QFN32 Packages QFP32 Packages QSOP24 Packages		30 26 80 65		°C/W °C/W °C/W
QFP32 Packages		80	_ 	°C/W
	-		_	
QSOP24 Packages	_	65		0000
				°C/W
QFN24 Packages		32.8	—	°C/W
QFN32 Packages		20	_	°C/W
QFP32 Packages		24.3	—	°C/W
QSOP24 Packages	_	38.1	_	°C/W
	QFP32 Packages	QFP32 Packages —	QFP32 Packages — 24.3	QFP32 Packages — 24.3 —

Table 4.20. Thermal Conditions

1. Thermal resistance assumes a multi-layer PCB with any exposed pad soldered to a PCB pad.

4.3 Absolute Maximum Ratings

Stresses above those listed in Table 4.21 Absolute Maximum Ratings on page 39 may cause permanent damage to the device. This is a stress rating only and functional operation of the devices at those or any other conditions above those indicated in the operation listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability. For more information on the available quality and reliability data, see the Quality and Reliability Monitor Report at http://www.silabs.com/support/quality/pages/default.aspx.

Table 4.21. Absolute Maximum Ratings

Parameter	Symbol	Test Condition	Min	Мах	Unit
Ambient Temperature Under Bias	T _{BIAS}		-55	125	°C
Storage Temperature	T _{STG}		-65	150	°C
Voltage on VDD	V _{DD}		GND-0.3	4.2	V
Voltage on VIO ²	V _{IO}		GND-0.3	V _{DD} +0.3	V
Voltage on I/O pins or RSTb, excluding	V _{IN}	V _{IO} > 3.3 V	GND-0.3	5.8	V
P2.0-P2.3 (QFN24 and QSOP24) or P3.0-P3.3 (QFN32 and QFP32)		V _{IO} < 3.3 V	GND-0.3	V _{IO} +2.5	V
Voltage on P2.0-P2.3 (QFN24 and QSOP24) or P3.0-P3.3 (QFN32 and QFP32)	V _{IN}		GND-0.3	V _{DD} +0.3	V
Total Current Sunk into Supply Pin	I _{VDD}		_	400	mA
Total Current Sourced out of Ground Pin	I _{GND}		400	_	mA
Current Sourced or Sunk by any I/O Pin or RSTb	I _{IO}		-100	100	mA
Operating Junction Temperature	TJ	T _A = -40 °C to 105 °C	-40	130	°C

Note:

1. Exposure to maximum rating conditions for extended periods may affect device reliability.

2. In certain package configurations, the VIO and VDD supplies are bonded to the same pin.

5. Typical Connection Diagrams

5.1 Power

Figure 5.1 Power Connection Diagram on page 40 shows a typical connection diagram for the power pins of the device.




Figure 5.1. Power Connection Diagram

5.2 Debug

The diagram below shows a typical connection diagram for the debug connections pins. The pin sharing resistors are only required if the functionality on the C2D (a GPIO pin) and the C2CK (RSTb) is routed to external circuitry. For example, if the RSTb pin is connected to an external switch with debouncing filter or if the GPIO sharing with the C2D pin is connected to an external circuit, the pin sharing resistors and connections to the debug adapter must be placed on the hardware. Otherwise, these components and connections can be omitted.

For more information on debug connections, see the example schematics and information available in *AN124: Pin Sharing Techniques* for the C2 Interface. Application notes can be found on the Silicon Labs website (http://www.silabs.com/8bit-appnotes) or in Simplicity Studio.




Figure 5.2. Debug Connection Diagram

5.3 Other Connections

Other components or connections may be required to meet the system-level requirements. Application Note AN203: "8-bit MCU Printed Circuit Board Design Notes" contains detailed information on these connections. Application Notes can be accessed on the Silicon Labs website (www.silabs.com/8bit-appnotes).

6. Pin Definitions

6.1 EFM8LB1x-QFN32 Pin Definitions




Figure 6.1. EFM8LB1x-QFN32 Pinout

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
1	P0.0	Multifunction I/O	Yes	P0MAT.0	VREF
				INT0.0	
				INT1.0	
				CLU0A.8	
				CLU2A.8	
				CLU3B.8	
2	VIO	I/O Supply Power Input			
3	VDD	Supply Power Input			
4	RSTb /	Active-low Reset /			
	C2CK	C2 Debug Clock			
5	P3.7 /	Multifunction I/O /			
	C2D	C2 Debug Data			
6	P3.4	Multifunction I/O			
7	P3.3	Multifunction I/O			DAC3
8	P3.2	Multifunction I/O			DAC2
9	P3.1	Multifunction I/O			DAC1
10	P3.0	Multifunction I/O			DAC0
11	P2.6	Multifunction I/O			ADC0.19
					CMP1P.8
					CMP1N.8
12	P2.5	Multifunction I/O		CLU3OUT	ADC0.18
					CMP1P.7
					CMP1N.7
13	P2.4	Multifunction I/O			ADC0.17
					CMP1P.6
					CMP1N.6
14	P2.3	Multifunction I/O	Yes	P2MAT.3	ADC0.16
				CLU1B.15	CMP1P.5
				CLU2B.15	CMP1N.5
				CLU3A.15	

Table 6.1. Pin Definitions for EFM8LB1x-QFN32

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
15	P2.2	Multifunction I/O	Yes	P2MAT.2	ADC0.15
				CLU2OUT	CMP1P.4
				CLU1A.15	CMP1N.4
				CLU2B.14	
				CLU3A.14	
16	P2.1	Multifunction I/O	Yes	P2MAT.1	ADC0.14
				I2C0_SCL	CMP1P.3
				CLU1B.14	CMP1N.3
				CLU2A.15	
				CLU3B.15	
17	P2.0	Multifunction I/O	Yes	P2MAT.0	CMP1P.2
				I2C0_SDA	CMP1N.2
				CLU1A.14	
				CLU2A.14	
				CLU3B.14	
18	P1.7	Multifunction I/O	Yes	P1MAT.7	ADC0.13
				CLU0B.15	CMP0P.9
				CLU1B.13	CMP0N.9
				CLU2A.13	
19	P1.6	Multifunction I/O	Yes	P1MAT.6	ADC0.12
				CLU0A.15	
				CLU1B.12	
				CLU2A.12	
20	P1.5	Multifunction I/O	Yes	P1MAT.5	ADC0.11
				CLU0B.14	
				CLU1A.13	
				CLU2B.13	
21	P1.4	Multifunction I/O	Yes	P1MAT.4	ADC0.10
				CLU0A.14	
				CLU1A.12	
				CLU2B.12	
22	P1.3	Multifunction I/O	Yes	P1MAT.3	ADC0.9
				CLU0B.13	
				CLU1B.11	
				CLU2B.11	
				CLU3A.13	

Pin	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
Number				Functions	
23	P1.2	Multifunction I/O	Yes	P1MAT.2	ADC0.8
				CLU0A.13	CMP0P.8
				CLU1A.11	CMP0N.8
				CLU2B.10	
				CLU3A.12	
24	P1.1	Multifunction I/O	Yes	P1MAT.1	ADC0.7
				CLU0B.12	CMP0P.7
				CLU1B.10	CMP0N.7
				CLU2A.11	
				CLU3B.13	
25	P1.0	Multifunction I/O	Yes	P1MAT.0	ADC0.6
				CLU1OUT	CMP0P.6
				CLU0A.12	CMP0N.6
				CLU1A.10	CMP1P.1
				CLU2A.10	CMP1N.1
				CLU3B.12	
26	P0.7	Multifunction I/O	Yes	P0MAT.7	ADC0.5
				INT0.7	CMP0P.5
				INT1.7	CMP0N.5
				CLU0B.11	CMP1P.0
				CLU1B.9	CMP1N.0
				CLU3A.11	
27	P0.6	Multifunction I/O	Yes	P0MAT.6	ADC0.4
				CNVSTR	CMP0P.4
				INT0.6	CMP0N.4
				INT1.6	
				CLU0A.11	
				CLU1B.8	
				CLU3A.10	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
28	P0.5	Multifunction I/O	Yes	P0MAT.5	ADC0.3
				INT0.5	CMP0P.3
				INT1.5	CMP0N.3
				UART0_RX	
				CLU0B.10	
				CLU1A.9	
				CLU3B.11	
29	P0.4	Multifunction I/O	Yes	P0MAT.4	ADC0.2
				INT0.4	CMP0P.2
				INT1.4	CMP0N.2
				UART0_TX	
				CLU0A.10	
				CLU1A.8	
				CLU3B.10	
30	P0.3	Multifunction I/O	Yes	P0MAT.3	EXTOSC
				EXTCLK	
				INT0.3	
				INT1.3	
				CLU0B.9	
				CLU2B.9	
				CLU3A.9	
31	P0.2	Multifunction I/O	Yes	P0MAT.2	ADC0.1
				INT0.2	CMP0P.1
				INT1.2	CMP0N.1
				CLU0OUT	
				CLU0A.9	
				CLU2B.8	
				CLU3A.8	
32	P0.1	Multifunction I/O	Yes	P0MAT.1	ADC0.0
				INT0.1	CMP0P.0
				INT1.1	CMP0N.0
				CLU0B.8	AGND
				CLU2A.9	
				CLU3B.9	
Center	GND	Ground			




Figure 6.2. EFM8LB1x-QFP32 Pinout

Table 6.2.	Pin Definitions	for EFM8LB1x-QFP32
------------	-----------------	--------------------

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
1	P0.0	Multifunction I/O	Yes	P0MAT.0	VREF
				INT0.0	
				INT1.0	
				CLU0A.8	
				CLU2A.8	
				CLU3B.8	
2	GND	Ground			
3	VIO	I/O Supply Power Input			
4	VDD	Supply Power Input			
5	RSTb /	Active-low Reset /			
	С2СК	C2 Debug Clock			

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
6	P3.7 /	Multifunction I/O /			
	C2D	C2 Debug Data			
7	P3.3	Multifunction I/O			DAC3
8	P3.2	Multifunction I/O			DAC2
9	P3.1	Multifunction I/O			DAC1
10	P3.0	Multifunction I/O			DAC0
11	P2.6	Multifunction I/O			ADC0.19
					CMP1P.8
					CMP1N.8
12	P2.5	Multifunction I/O		CLU3OUT	ADC0.18
					CMP1P.7
					CMP1N.7
13	P2.4	Multifunction I/O			ADC0.17
					CMP1P.6
					CMP1N.6
14	P2.3	Multifunction I/O	Yes	P2MAT.3	ADC0.16
				CLU1B.15	CMP1P.5
				CLU2B.15	CMP1N.5
				CLU3A.15	
15	P2.2	Multifunction I/O	Yes	P2MAT.2	ADC0.15
				CLU2OUT	CMP1P.4
				CLU1A.15	CMP1N.4
				CLU2B.14	
				CLU3A.14	
16	P2.1	Multifunction I/O	Yes	P2MAT.1	ADC0.14
				I2C0_SCL	CMP1P.3
				CLU1B.14	CMP1N.3
				CLU2A.15	
				CLU3B.15	
17	P2.0	Multifunction I/O	Yes	P2MAT.0	CMP1P.2
				I2C0_SDA	CMP1N.2
				CLU1A.14	
				CLU2A.14	
				CLU3B.14	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
18	P1.7	Multifunction I/O	Yes	P1MAT.7	ADC0.13
				CLU0B.15	CMP0P.9
				CLU1B.13	CMP0N.9
				CLU2A.13	
19	P1.6	Multifunction I/O	Yes	P1MAT.6	ADC0.12
				CLU0A.15	
				CLU1B.12	
				CLU2A.12	
20	P1.5	Multifunction I/O	Yes	P1MAT.5	ADC0.11
				CLU0B.14	
				CLU1A.13	
				CLU2B.13	
21	P1.4	Multifunction I/O	Yes	P1MAT.4	ADC0.10
				CLU0A.14	
				CLU1A.12	
				CLU2B.12	
22	P1.3	Multifunction I/O	Yes	P1MAT.3	ADC0.9
				CLU0B.13	
				CLU1B.11	
				CLU2B.11	
				CLU3A.13	
23	P1.2	Multifunction I/O	Yes	P1MAT.2	ADC0.8
				CLU0A.13	CMP0P.8
				CLU1A.11	CMP0N.8
				CLU2B.10	
				CLU3A.12	
24	P1.1	Multifunction I/O	Yes	P1MAT.1	ADC0.7
				CLU0B.12	CMP0P.7
				CLU1B.10	CMP0N.7
				CLU2A.11	
				CLU3B.13	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
25	P1.0	Multifunction I/O	Yes	P1MAT.0	ADC0.6
				CLU1OUT	CMP0P.6
				CLU0A.12	CMP0N.6
				CLU1A.10	CMP1P.1
				CLU2A.10	CMP1N.1
				CLU3B.12	
26	P0.7	Multifunction I/O	Yes	P0MAT.7	ADC0.5
				INT0.7	CMP0P.5
				INT1.7	CMP0N.5
				CLU0B.11	CMP1P.0
				CLU1B.9	CMP1N.0
				CLU3A.11	
27	P0.6	Multifunction I/O	Yes	P0MAT.6	ADC0.4
				CNVSTR	CMP0P.4
				INT0.6	CMP0N.4
				INT1.6	
				CLU0A.11	
				CLU1B.8	
				CLU3A.10	
28	P0.5	Multifunction I/O	Yes	P0MAT.5	ADC0.3
				INT0.5	CMP0P.3
				INT1.5	CMP0N.3
				UART0_RX	
				CLU0B.10	
				CLU1A.9	
				CLU3B.11	
29	P0.4	Multifunction I/O	Yes	P0MAT.4	ADC0.2
				INT0.4	CMP0P.2
				INT1.4	CMP0N.2
				UART0_TX	
				CLU0A.10	
				CLU1A.8	
				CLU3B.10	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
30	P0.3	Multifunction I/O	Yes	P0MAT.3	EXTOSC
				EXTCLK	
				INT0.3	
				INT1.3	
				CLU0B.9	
				CLU2B.9	
				CLU3A.9	
31	P0.2	Multifunction I/O	Yes	P0MAT.2	ADC0.1
				INT0.2	CMP0P.1
				INT1.2	CMP0N.1
				CLU0OUT	
				CLU0A.9	
				CLU2B.8	
				CLU3A.8	
32	P0.1	Multifunction I/O	Yes	P0MAT.1	ADC0.0
				INT0.1	CMP0P.0
				INT1.1	CMP0N.0
				CLU0B.8	AGND
				CLU2A.9	
				CLU3B.9	






Table 6.3.	Pin Definitions	for EFM8LB1x-QFN24
------------	-----------------	--------------------

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
1	P0.1	Multifunction I/O	Yes	P0MAT.1	ADC0.0
				INT0.1	CMP0P.0
				INT1.1	CMP0N.0
				CLU0B.8	AGND
				CLU2A.9	
				CLU3B.9	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
2	P0.0	Multifunction I/O	Yes	P0MAT.0	VREF
				INT0.0	
				INT1.0	
				CLU0A.8	
				CLU2A.8	
				CLU3B.8	
3	GND	Ground			
4	VDD / VIO	Supply Power Input			
5	RSTb /	Active-low Reset /			
	C2CK	C2 Debug Clock			
6	P3.0 /	Multifunction I/O /			
	C2D	C2 Debug Data			
7	P2.3	Multifunction I/O	Yes	P2MAT.3	DAC3
				CLU1B.15	
				CLU2B.15	
				CLU3A.15	
8	P2.2	Multifunction I/O	Yes	P2MAT.2	DAC2
				CLU1A.15	
				CLU2B.14	
				CLU3A.14	
9	P2.1	Multifunction I/O	Yes	P2MAT.1	DAC1
				CLU1B.14	
				CLU2A.15	
				CLU3B.15	
10	P2.0	Multifunction I/O	Yes	P2MAT.0	DAC0
				CLU1A.14	
				CLU2A.14	
				CLU3B.14	
11	P1.6	Multifunction I/O	Yes	P1MAT.6	ADC0.11
				CLU3OUT	CMP1P.5
				CLU0A.15	CMP1N.5
				CLU1B.12	
				CLU2A.12	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
12	P1.5	Multifunction I/O	Yes	P1MAT.5	ADC0.10
				CLU2OUT	CMP1P.4
				CLU0B.14	CMP1N.4
				CLU1A.13	
				CLU2B.13	
13	P1.4	Multifunction I/O	Yes	P1MAT.4	ADC0.9
				I2C0_SCL	CMP1P.3
				CLU0A.14	CMP1N.3
				CLU1A.12	
				CLU2B.12	
14	P1.3	Multifunction I/O	Yes	P1MAT.3	CMP1P.2
				I2C0_SDA	CMP1N.2
				CLU0B.13	
				CLU1B.11	
				CLU2B.11	
				CLU3A.13	
15	GND	Ground			
16	P1.2	Multifunction I/O	Yes	P1MAT.2	ADC0.8
				CLU0A.13	
				CLU1A.11	
				CLU2B.10	
				CLU3A.12	
17	P1.1	Multifunction I/O	Yes	P1MAT.1	ADC0.7
				CLU0B.12	
				CLU1B.10	
				CLU2A.11	
				CLU3B.13	
18	P1.0	Multifunction I/O	Yes	P1MAT.0	ADC0.6
				CLU0A.12	
				CLU1A.10	
				CLU2A.10	
				CLU3B.12	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
19	P0.7	Multifunction I/O	Yes	P0MAT.7	ADC0.5
				INT0.7	CMP0P.5
				INT1.7	CMP0N.5
				CLU1OUT	CMP1P.1
				CLU0B.11	CMP1N.1
				CLU1B.9	
				CLU3A.11	
20	P0.6	Multifunction I/O	Yes	P0MAT.6	ADC0.4
				CNVSTR	CMP0P.4
				INT0.6	CMP0N.4
				INT1.6	CMP1P.0
				CLU0A.11	CMP1N.0
				CLU1B.8	
				CLU3A.10	
21	P0.5	Multifunction I/O	Yes	P0MAT.5	ADC0.3
				INT0.5	CMP0P.3
				INT1.5	CMP0N.3
				UART0_RX	
				CLU0B.10	
				CLU1A.9	
				CLU3B.11	
22	P0.4	Multifunction I/O	Yes	P0MAT.4	ADC0.2
				INT0.4	CMP0P.2
				INT1.4	CMP0N.2
				UART0_TX	
				CLU0A.10	
				CLU1A.8	
				CLU3B.10	
23	P0.3	Multifunction I/O	Yes	P0MAT.3	EXTOSC
				EXTCLK	
				INT0.3	
				INT1.3	
				CLU0B.9	
				CLU2B.9	
				CLU3A.9	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
24	P0.2	Multifunction I/O	Yes	P0MAT.2	ADC0.1
				INT0.2	CMP0P.1
				INT1.2	CMP0N.1
				CLU0OUT	
				CLU0A.9	
				CLU2B.8	
				CLU3A.8	
Center	GND	Ground			




Figure 6.4. EFM8LB1x-QSOP24 Pinout

Table 6.4.	. Pin Definitions for EFM8LB1x-Q	SOP24
------------	----------------------------------	-------

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
1	P0.3	Multifunction I/O	Yes	P0MAT.3	EXTOSC
				EXTCLK	
				INT0.3	
				INT1.3	
				CLU0B.9	
				CLU2B.9	
				CLU3A.9	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
2	P0.2	Multifunction I/O	Yes	P0MAT.2	ADC0.1
				INT0.2	CMP0P.1
				INT1.2	CMP0N.1
				CLU0OUT	
				CLU0A.9	
				CLU2B.8	
				CLU3A.8	
3	P0.1	Multifunction I/O	Yes	P0MAT.1	ADC0.0
				INT0.1	CMP0P.0
				INT1.1	CMP0N.0
				CLU0B.8	AGND
				CLU2A.9	
				CLU3B.9	
4	P0.0	Multifunction I/O	Yes	P0MAT.0	VREF
				INT0.0	
				INT1.0	
				CLU0A.8	
				CLU2A.8	
				CLU3B.8	
5	GND	Ground			
6	VDD / VIO	Supply Power Input			
7	RSTb /	Active-low Reset /			
	C2CK	C2 Debug Clock			
8	P3.0 /	Multifunction I/O /			
	C2D	C2 Debug Data			
9	P2.3	Multifunction I/O	Yes	P2MAT.3	DAC3
				CLU1B.15	
				CLU2B.15	
				CLU3A.15	
10	P2.2	Multifunction I/O	Yes	P2MAT.2	DAC2
				CLU1A.15	
				CLU2B.14	
				CLU3A.14	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
11	P2.1	Multifunction I/O	Yes	P2MAT.1	DAC1
				CLU1B.14	
				CLU2A.15	
				CLU3B.15	
12	P2.0	Multifunction I/O	Yes	P2MAT.0	DAC0
				CLU1A.14	
				CLU2A.14	
				CLU3B.14	
13	P1.7	Multifunction I/O	Yes	P1MAT.7	ADC0.12
				CLU0B.15	CMP1P.6
				CLU1B.13	CMP1N.6
				CLU2A.13	
14	P1.6	Multifunction I/O	Yes	P1MAT.6	ADC0.11
				CLU3OUT	CMP1P.5
				CLU0A.15	CMP1N.5
				CLU1B.12	
				CLU2A.12	
15	P1.5	Multifunction I/O	Yes	P1MAT.5	ADC0.10
				CLU2OUT	CMP1P.4
				CLU0B.14	CMP1N.4
				CLU1A.13	
				CLU2B.13	
16	P1.4	Multifunction I/O	Yes	P1MAT.4	ADC0.9
				I2C0_SCL	CMP1P.3
				CLU0A.14	CMP1N.3
				CLU1A.12	
				CLU2B.12	
17	P1.3	Multifunction I/O	Yes	P1MAT.3	CMP1P.2
				I2C0_SDA	CMP1N.2
				CLU0B.13	
				CLU1B.11	
				CLU2B.11	
				CLU3A.13	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
18	P1.2	Multifunction I/O	Yes	P1MAT.2	ADC0.8
				CLU0A.13	
				CLU1A.11	
				CLU2B.10	
				CLU3A.12	
19	P1.1	Multifunction I/O	Yes	P1MAT.1	ADC0.7
				CLU0B.12	
				CLU1B.10	
				CLU2A.11	
				CLU3B.13	
20	P1.0	Multifunction I/O	Yes	P1MAT.0	ADC0.6
				CLU0A.12	
				CLU1A.10	
				CLU2A.10	
				CLU3B.12	
21	P0.7	Multifunction I/O	Yes	P0MAT.7	ADC0.5
				INT0.7	CMP0P.5
				INT1.7	CMP0N.5
				CLU1OUT	CMP1P.1
				CLU0B.11	CMP1N.1
				CLU1B.9	
				CLU3A.11	
22	P0.6	Multifunction I/O	Yes	P0MAT.6	ADC0.4
				CNVSTR	CMP0P.4
				INT0.6	CMP0N.4
				INT1.6	CMP1P.0
				CLU0A.11	CMP1N.0
				CLU1B.8	
				CLU3A.10	

Pin Number	Pin Name	Description	Crossbar Capability	Additional Digital Functions	Analog Functions
23	P0.5	Multifunction I/O	Yes	P0MAT.5	ADC0.3
				INT0.5	CMP0P.3
				INT1.5	CMP0N.3
				UART0_RX	
				CLU0B.10	
				CLU1A.9	
				CLU3B.11	
24	P0.4	Multifunction I/O	Yes	P0MAT.4	ADC0.2
				INT0.4	CMP0P.2
				INT1.4	CMP0N.2
				UART0_TX	
				CLU0A.10	
				CLU1A.8	
				CLU3B.10	

7. QFN32 Package Specifications

7.1 Package Dimensions




Figure 7.1. Package Drawing

Table 7.1.	Package	Dimensions
------------	---------	------------

Dimension	Min	Тур	Мах
A	0.45	0.50	0.55
A1	0.00	0.035	0.05
b	0.15	0.20	0.25
D		4.00 BSC.	
D2	2.80	2.90	3.00
е	0.40 BSC.		
E	4.00 BSC.		
E2	2.80	2.90	3.00
L	0.20	0.30	0.40
ааа	—	—	0.10
bbb	—	—	0.10
ссс	_	_	0.08
ddd	—	—	0.10
eee	—	—	0.10
999	_		0.05

Dimension	Min	Тур	Мах
Note:			
1. All dimensions shown are in millimeters (mm) unless otherwise noted.			
2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.			
3. This drawing conforms to JEDEC Solid State Outline MO-220.			
4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020C specification for Small Body Components.			

7.2 PCB Land Pattern




Figure 7.2. PCB Land Pattern Drawing

Table 7.0	DCB Land Dattary Dimensions	
Table 7.2.	PCB Land Pattern Dimensions	, i

Dimension	Min	Мах
C1	—	4.10
C2	—	4.10
X1	_	0.2
X2	_	3.0
Y1	_	0.7
Y2	_	3.0
e	_	0.4

Dimension	Min	Мах
Note:		
1. All dimensions shown are in millimeters	(mm) unless otherwise noted.	
2. Dimensioning and Tolerancing is per the	ANSI Y14.5M-1994 specification.	
3. This Land Pattern Design is based on th	e IPC-7351 guidelines.	
 All dimensions shown are at Maximum N cation Allowance of 0.05mm. 	Naterial Condition (MMC). Least Material Con	dition (LMC) is calculated based on a Fabri
All metal pads are to be non-solder mas minimum, all the way around the pad.	k defined (NSMD). Clearance between the so	older mask and the metal pad is to be 60 μ n
6. A stainless steel, laser-cut and electro-p	olished stencil with trapezoidal walls should b	be used to assure good solder paste release
7. The stencil thickness should be 0.125 mm (5 mils).		
8. The ratio of stencil aperture to land pad size should be 1:1 for all perimeter pads.		
9. A 2 x 2 array of 1.10 mm square opening	gs on a 1.30 mm pitch should be used for the	center pad.
40. A Na Olasan Turas 0 salidar nasta is recommended		

- 10. A No-Clean, Type-3 solder paste is recommended.
- 11. The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

7.3 Package Marking




Figure 7.3. Package Marking

The package marking consists of:

- PPPPPPP The part number designation.
- TTTTTT A trace or manufacturing code.
- YY The last 2 digits of the assembly year.
- WW The 2-digit workweek when the device was assembled.
- # The device revision (A, B, etc.).

8. QFP32 Package Specifications

8.1 Package Dimensions






Table 8.1. Package Dimensions

Dimension	Min	Тур	Мах
A	_	—	1.20
A1	0.05	_	0.15
A2	0.95	1.00	1.05
b	0.30	0.37	0.45
С	0.09	—	0.20
D	9.00 BSC		
D1	7.00 BSC		
е	0.80 BSC		
E	9.00 BSC		

Dimension	Min	Тур	Мах	
E1		7.00 BSC		
L	0.50	0.60	0.70	
ааа		0.20		
bbb		0.20		
CCC	0.10			
ddd		0.20		
theta	0°	3.5°	7°	
NI 4				

Note:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. This drawing conforms to JEDEC outline MS-026.

4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

8.2 PCB Land Pattern




Figure 8.2. PCB Land Pattern Drawing

Table 8.2. PCB L	Land Pattern	Dimensions
------------------	--------------	------------

Dimension	Min	Мах
C1	8.40	8.50
C2	8.40	8.50
E	0.80 BSC	
X1	0.55	
Y1	1.5	

Note:

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. This Land Pattern Design is based on the IPC-7351 guidelines.
- 3. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 µm minimum, all the way around the pad.
- 4. A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 5. The stencil thickness should be 0.125 mm (5 mils).
- 6. The ratio of stencil aperture to land pad size should be 1:1 for all perimeter pads.
- 7. A No-Clean, Type-3 solder paste is recommended.

8. The recommended card reflow profile is per the JEDEC/IPC J-STD-020C specification for Small Body Components.




Figure 8.3. Package Marking

The package marking consists of:

- PPPPPPP The part number designation.
- TTTTTT A trace or manufacturing code.
- YY The last 2 digits of the assembly year.
- WW The 2-digit workweek when the device was assembled.
- # The device revision (A, B, etc.).

9. QFN24 Package Specifications

9.1 Package Dimensions




Figure 9.1. Package Drawing

Dimension	Min	Тур	Мах
A	0.8	0.85	0.9
A1	0.00	—	0.05
A2		0.65	_
A3		0.203 REF	
b	0.15	0.2	0.25
b1	0.25	0.3	0.35
D		3.00 BSC	
E		3.00 BSC	
е	0.40 BSC		
e1		0.45 BSC	
J	1.60	1.70	1.80
К	1.60	1.70	1.80
L	0.35	0.40	0.45
L1	0.25	0.30	0.35
ааа		0.10	_
bbb	_	0.10	—
ссс	_	0.08	_
ddd	_	0.1	—
eee	_	0.1	—

Table 9.1. Package Dimensions

Note:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. This drawing conforms to JEDEC Solid State Outline MO-248 but includes custom features which are toleranced per supplier designation.

4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

9.2 PCB Land Pattern




Figure 9.2. PCB Land Pattern Drawing

Table 9.2. PCB Land Pattern Dimensions

Dimension	Min	Мах	
C1	3.00		
C2	3.0	00	
е	0.4 F	REF	
X1	0.20		
X2	1.80		
Y1	0.80		
Y2	1.80		
Y3	0.4		
f	2.50 REF		

Dimension	Min	Max
с	0.25	0.35

Note:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

- 2. Dimensioning and Tolerancing is per the ANSI Y14.5M-1994 specification.
- 3. This Land Pattern Design is based on the IPC-SM-782 guidelines.
- 4. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 μm minimum, all the way around the pad.
- 5. A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 6. The stencil thickness should be 0.125 mm (5 mils).
- 7. The ratio of stencil aperture to land pad size should be 1:1 for all perimeter pads.
- 8. A 2 x 1 array of 0.7 mm x 1.6 mm openings on a 0.9 mm pitch should be used for the center pad.
- 9. A No-Clean, Type-3 solder paste is recommended.
- 10. The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

9.3 Package Marking




Figure 9.3. Package Marking

The package marking consists of:

- PPPPPPP The part number designation.
- TTTTTT A trace or manufacturing code.
- YY The last 2 digits of the assembly year.
- WW The 2-digit workweek when the device was assembled.
- # The device revision (A, B, etc.).

10. QSOP24 Package Specifications

10.1 Package Dimensions




Figure 10.1. Package Drawing

Table 10.1. Package Dimensions

Dimension	Min	Тур	Мах
A	_	_	1.75
A1	0.10	—	0.25
b	0.20	_	0.30
С	0.10	_	0.25
D	8.65 BSC		
E	6.00 BSC		
E1	3.90 BSC		
e	0.635 BSC		
L	0.40	_	1.27

Dimension	Min	Тур	Мах
theta	0°	_	8°
ааа		0.20	
bbb	0.18		
ссс	0.10		
ddd	0.10		
Note:			

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. This drawing conforms to JEDEC outline MO-137, variation AE.

4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

10.2 PCB Land Pattern




Figure 10.2. PCB Land Pattern Drawing

Table 10.2. PCB Land Pattern Dimensions

Dimension	Min	Мах	
С	5.20	5.30	
E	0.635 BSC		
X	0.30	0.40	
Y	1.50	1.60	

Note:

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. This land pattern design is based on the IPC-7351 guidelines.
- 3. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 µm minimum, all the way around the pad.
- 4. A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 5. The stencil thickness should be 0.125 mm (5 mils).
- 6. The ratio of stencil aperture to land pad size should be 1:1 for all perimeter pads.
- 7. A No-Clean, Type-3 solder paste is recommended.
- 8. The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

10.3 Package Marking



Figure 10.3. Package Marking

The package marking consists of:

- PPPPPPP The part number designation.
- TTTTTT A trace or manufacturing code.
- YY The last 2 digits of the assembly year.
- WW The 2-digit workweek when the device was assembled.
- # The device revision (A, B, etc.).

11. Revision History

Revision 1.4

March, 2024

- Added missing 4.1.18 SPI electrical specifications.
- Noted that all QSOP Package OPNs are EOL.

Revision 1.3

December 2018

- Updated ordering part numbers to revision C.
- Updated 1. Feature List, Figure 3.1 Detailed EFM8LB1 Block Diagram on page 8, and 3.4 Clocking to removed external crystal oscillator as clock source.
- Updated 4.1.8 External Oscillator for RC oscillator specifications.
- Updated 3.10 Bootloader recommendations for production programming.
- Added more information about documentation to the 3.1 Introduction section.
- Removed all references to XTAL and renamed it to EXTOSC.

Revision 1.2

January 2018

- Added S1 devices. Updated 2. Ordering Information and 3.10 Bootloader with the new S1 device information.
- Updated 3.1 Introduction to mention all device documentation.
- Updated 4.1.1 Recommended Operating Conditions to remove the "GPIO levels are undefined whenever VIO is less than 1 V" note, added a new minimum for VIO, and added a note referencing 4.1.16 Port I/O.
- Added a note to Table 4.2 Power Consumption on page 19 providing more information about the Comparator Reference specification.
- Renamed Thermal Resistance to Thermal Resistance (Junction to Ambient) and added Thermal Resistance (Junction to Case) to 4.2 Thermal Conditions.
- Updated the revision history format.

Revision 1.1

March 2017

- Removed the note that AEC-Q100 qualification is pending from 1. Feature List and 2. Ordering Information.
- Added 4.1.12 1.8 V Internal LDO Voltage Regulator.
- Added a note to 4.1.9 ADC specifying the production test VREF and ground setup.
- Added Output Voltage and Output Current specifications to 4.1.13 DACs.
- Fixed the Symbol and Test Condition values for Output Noise in 4.1.13 DACs.
- Updated the minimum VIO displayed in Figure 5.1 Power Connection Diagram on page 40 to match the specification in 4.1.1 Recommended Operating Conditions.
- Added a note to 3.1 Introduction referencing the Reference Manual.
- Corrected the application note number for AN124: Pin Sharing Techniques for the C2 Interface in 5.2 Debug.
- Adjusted the Data Hold and Data Setup Times in 4.1.17 SMBus and added a note referring to the DLYEXT bit.

Revision 1.01

October 2016

• Updated QFN24 center pad stencil description.

Revision 1.0

September 2016

- Updated part numbers to revision B.
- Updated many specifications with full characterization data.
- Added a note regarding which DACs are available to Table 2.1 Product Selection Guide on page 3.
- Added specifications for 4.1.17 SMBus.
- Added bootloader pinout information to 3.10 Bootloader.
- Added CRC Calculation Time to 4.1.4 Flash Memory.

Revision 0.5

February 2016

- Updated Figure 5.2 Debug Connection Diagram on page 41 to move the pull-up resistor on C2D / RSTb to after the series resistor instead of before.
- Added S0 devices and information about the SMBus bootloader in 3.10 Bootloader.
- Added a reference to AN945: EFM8 Factory Bootloader User Guide in 3.10 Bootloader.
- · Added mention of the pre-programmed bootloaders in 1. Feature List.
- Updated all part numbers to revision B.
- · Added the C oscillator, which is now available on revision B.
- Adjusted C1, C2, X2, Y2, and Y1 maximums for 7.2 PCB Land Pattern.
- · Adjusted package markings for QFN32 and QSOP24 packages.
- Filled in TBD minimum and maximum values for DAC Differential Nonlinearity in Table 4.13 DACs on page 29.

Revision 0.4

- · Updated specification tables based on current device characterization status and production test limits.
- Added bootloader section.
- Added typical connection diagrams.
- · Corrected CLU connections in pin function tables.

Revision 0.3

- Added information on the bootloader to 3.10 Bootloader.
- Updated some characterization TBD values.

Revision 0.1

· Initial release.

Simplicity Studio

One-click access to MCU and wireless tools, documentation, software, source code libraries & more. Available for Windows, Mac and Linux!



www.silabs.com/IoT



www.silabs.com/simplicity



www.silabs.com/quality



Support & Community www.silabs.com/community

Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice to the product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Without prior notification, Silicon Labs may update product firmware during the manufacturing process for security or reliability reasons. Such changes will not alter the specifications or the performance of the product. Silicon Labs shall have no liability for the consequences of use of the information supplied in this document. This document does not imply or expressly grant any license to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any FDA Class III devices, applications for which FDA premarket approval is required or Life Support Systems without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Labs products are not designed or authorized for military applications. Silicon Labs product shall under no circumstances be used in weapons of mass destruction including (but not limited to) nuclear, biological or chemical weapons, or missiles capable of delivering such weapons. Silicon Labs disclaims all express and implied warranties and shall not be responsible or liable for any injuries or damages related to use of a Silicon Lab

Trademark Information

Silicon Laboratories Inc.[®], Silicon Laboratories[®], Silicon Labs[®], SiLabs[®] and the Silicon Labs logo[®], Bluegiga[®], Bluegiga Logo[®], EFM[®], EFM32[®], EFR, Ember[®], Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Redpine Signals[®], WiSeConnect, n-Link, ThreadArch[®], EZLink[®], EZRadio[®], EZRadio[®], Gecko[®], Gecko OS, Gecko OS Studio, Precision32[®], Simplicity Studio[®], Telegesis, the Telegesis Logo[®], USBXpress[®], Zentri, the Zentri logo and Zentri DMS, Z-Wave[®], and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc. 400 West Cesar Chavez Austin, TX 78701 USA

www.silabs.com